QUADRIOS

TECHNICAL DATA SHEET

www.quadrios.de

Double-sided adhesive Pad / Tape
Item-No.: 26SA148 … 26SA184



Ideal for permanently securing objects to smooth surfaces without drilling, nailing, or clamping. This adhesive dot has strong holding power, provides excellent grip, and is also very durable and resistant to environmental factors. The material, made of pure EVA foam, compensates for minor unevenness and also has a certain degree of vibration-damping effect. Combined with the high-quality 3M adhesive film, this results in a combination of durability and reliability.

Excellent and long-lasting adhesion to clean, grease- and oil-free, dry, smooth surfaces. Not suitable for porous, uneven, or textured surfaces or fabrics (brick, wallpaper, plaster, plush fabric, textiles, etc.). If the adhesive tape needs to be removed, pre-treating temperature-resistant surfaces with a hair dryer or heat gun is recommended. Adhesive strength increases over time - initial adhesion is immediate, and approximately 50% of the final strength is achieved after 30 minutes. Depending on environmental conditions, full adhesion is achieved after 2 to 3 days. Optimal application temperature: approx. 20 to 35 °C. When applied correctly, it remains stable at ambient temperatures ranging from -20 to +80 °C.

Technical Specifications

Material: EVA-Foam • Thickness: 3 mm • Adhesive surface: 3M 9448A • Color: White, Black • Shape versions: Circle, Square, Rectangular, Tape/Roll • Ambient temp. -20 … +80 °C.

Item No.	Description	Color	Form	Dimensions	Content	EAN
26SA148	Double-sided adhesive pad, white Ø 20 mm 10 pcs.	White	Circle	Ø 20 mm	10 pcs.	4262511627046
26SA149	Double-sided adhesive pad, white Ø 30 mm 10 pcs.	White	Circle	Ø 30 mm	10 pcs.	4262511627053
26SA150	Double-sided adhesive pad, white Ø 40 mm 10 pcs.	White	Circle	Ø 40 mm	10 pcs.	4262511627060
26SA151	Double-sided adhesive pad, white Ø 50 mm 10 pcs.	White	Circle	Ø 50 mm	10 pcs.	4262511627077
26SA152	Double-sided adhesive pad, white 20x20 mm 10 pcs.	White	Square	20 x 20 mm	10 pcs.	4262511627084
26SA153	Double-sided adhesive pad, white 30x30mm 10pcs.	White	Square	30 x 30 mm	10 pcs.	4262511627091
26SA154	Double-sided adhesive pad, white 40x40mm 10pcs.	White	Square	40 x 40 mm	10 pcs.	4262511627107
26SA155	Double-sided adhesive pad, white 50x50mm 10pcs.	White	Square	50 x 50 mm	10 pcs.	4262511627114
26SA156	Double-sided adhesive pad, white 100x100mm 10pcs.	White	Square	100 x 100 mm	10 pcs.	4262511627121
26SA157	Double-sided adhesive pad, white 30x50mm 10pcs.	White	Rectangular	30 x 50 mm	10 pcs.	4262511627138
26SA158	Double-sided adhesive pad, white 30x100mm 10pcs.	White	Rectangular	30 x 100 mm	10 pcs.	4262511627145
26SA159	Double-sided adhesive pad, white 100x150mm 1pc.	White	Rectangular	100 x 150 mm	1 pc.	4262511627152
26SA160	Double-sided adhesive pad, white 150x200mm 1pc.	White	Rectangular	150 x 200 mm	1 pc.	4262511627169
26SA161	Double-sided adhesive pad, white 200x250mm 1pc.	White	Rectangular	200 x 250 mm	1 pc.	4262511627176
26SA162	Double-sided adhesive pad, white 148x210mm (A5) 1 pc.	White	Rectangular	A5 (148 x 210 mm)	1 pc.	4262511627183
26SA163	Double-sided adhesive pad, white 297x210mm (A4) 1 pc.	White	Rectangular	A4 (297 x 210 mm)	1 pc.	4262511627190
26SA164	Double-sided adhesive pad, wt 20x Ø 30mm & 20x 4x4cm	White	Circle/Square	20x Ø 30 mm + 20x 40 x 40 mm	40 pcs.	4262511627206
26SA165	Double-sided adhesive tape white 10 mm x 5 m 1 pc.	White	Roll	10 mm x 5 m	1 pc.	4262511627213
26SA166	Double-sided adhesive tape white 25 mm x 5 m 1 pc.	White	Roll	25 mm x 5 m	1 pc.	4262511627220
26SA167	Double-sided adhesive tape white 50 mm x 5 m 1 pc.	White	Roll	50 mm x 5 m	1 pc.	4262511627237

Continue next page

This is a publication by Quadrios GmbH • Bahnhofstraße 16 • D-92670 Windischeschenbach (www.quadrios.de)
All right including translation reserved. Reproduction by any method or the capture in electronic data processing system require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.
All statements without guarantee
© Quadrios GmbH
Version 2026/04

Item No.	Description	Color	Form	Dimensions	Content	EAN
26SA168	Double-sided adhesive pad, black Ø 20 mm 10 pcs.	Black	Circle	Ø 20 mm	10 pcs.	4262511627244
26SA169	Double-sided adhesive pad, black Ø 30 mm 10 pcs.	Black	Circle	Ø 30 mm	10 pcs.	4262511627251
26SA170	Double-sided adhesive pad, black Ø 40 mm 10 pcs.	Black	Circle	Ø 40 mm	10 pcs.	4262511627268
26SA171	Double-sided adhesive pad, black Ø 50 mm 10 pcs.	Black	Circle	Ø 50 mm	10 pcs.	4262511627275
26SA172	Double-sided adhesive pad, black 20x20 mm 10 pcs.	Black	Square	20 x 20 mm	10 pcs.	4262511627282
26SA173	Double-sided adhesive pad, black 30x30 mm 10 pcs.	Black	Square	30 x 30 mm	10 pcs.	4262511627299
26SA174	Double-sided adhesive pad, black 40x40 mm 10 pcs.	Black	Square	40 x 40 mm	10 pcs.	4262511627305
26SA175	Double-sided adhesive pad, black 50x50 mm 10 pcs.	Black	Square	50 x 50 mm	10 pcs.	4262511627312
26SA176	Double-sided adhesive pad, black 100x100 mm 10 pcs.	Black	Square	100 x 100 mm	10 pcs.	4262511627329
26SA177	Double-sided adhesive pad, black 30x50 mm 10 pcs.	Black	Rectangular	30 x 50 mm	10 pcs.	4262511627336
26SA178	Double-sided adhesive pad, black 30x100 mm 10 pcs.	Black	Rectangular	30 x 100 mm	10 pcs.	4262511627343
26SA179	Double-sided adhesive pad, black 100x150 mm 1 pc.	Black	Rectangular	100 x 150 mm	1 pc.	4262511627350
26SA180	Double-sided adhesive pad, black 150x200 mm 1 pc.	Black	Rectangular	150 x 200 mm	1 pc.	4262511627367
26SA181	Double-sided adhesive pad, black 200x250 mm 1 pc.	Black	Rectangular	200 x 250 mm	1 pc.	4262511627374
26SA182	Double-sided adhesive pad, black 148x210 mm (A5) 1 pc.	Black	Rectangular	A5 (148 x 210 mm)	1 pc.	4262511627381
26SA183	Double-sided adhesive pad, black 297x210 mm (A4) 1 pc.	Black	Rectangular	A4 (297 x 210 mm)	1 pc.	4262511627398
26SA184	Double-sided adhesive pad, bk 20x Ø 30 mm & 20x 4x4cm	Black	Circle/Square	20x Ø 30 mm + 20x 40 x 40 mm	40 pcs.	4262511627404

This is a publication by Quadrios GmbH • Bahnhofstraße 16 • D-92670 Windischeschenbach (www.quadrios.de)

All right including translation reserved. Reproduction by any method or the capture in electronic data processing system require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

All statements without guarantee

© Quadrios GmbH

Version 2026/04