Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision	Unit
1.	Supplier's name or trademark.	BenQ	
	Supplier's address.	BenQ Europe B.V. , Meere-nakkerweg, 1-17 5652 AR Eindhoven Noord-Brabant Netherlands	
2.	Model identifier	MA270S	
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	F	
4.	On mode power demand in SDR	25,2	W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	G	
6.	On mode power demand in HDR, if implemented	28,2	W
7.	Off mode, power demand, if applicable	0,3	W
8.	Standby mode power demand, if applicable	0,5	W
9.	Networked standby mode power demand, if applic-able	n.a.	W
10.	Electronic display category	Monitor	
11.	Size ratio	16 : 9	
12.	Screen resolution	5 120 x 2 880	pixels
13.	Screen diagonal	68,5	cm
14.	Screen diagonal	27	inches
15.	Visible screen area	20,0	dm^2
16.	Panel technology used	LED LCD	
17.	Automatic Brightness Control (ABC) available	No	
18.	Voice recognition sensor available	No	
19.	Room presence sensor available	No	
20.	Image refresh frequency rate (default)	60	Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	8	Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the mar-ket)	7	Years
23.	Minimum guaranteed product support	7	Years
	Minimum duration of the general guarantee offered by the supplier	2	Years
24.	Power supply type	Internal	
25.	External power supply (non standardized and included in the product box)		
	i -		

	ii	Input voltage	-	V
	iii	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	i	-		
	ii	Required output voltage	-	V
	iii	Required delivered current (minimum)	-	A
	iv	Required current frequency	-	Hz

EPREL registration number: 2526285

Model placed on the Union market from 09/12/2025.

https://eprel.ec.europa.eu/qr/2526285

Supplier: BenQ Europe B.V. (Manufacturer) **Website:** www.benq.eu

Customer care service:

Name: BenQ Europe B.V. **Website:** https://www.benq.eu

Email: energy.label@benq.eu **Phone:** +31-88-8889200

Address:
Meerenakkerweg, 1-17 5652 AR Eindhoven Noord-Brabant Netherlands