


83259896	DATA SHEET	
Valid from: 18.09.2018	FLEXIMARK® THERMAL TRANSFER KIT	

FLEXIMARK® THERMAL TRANSFER KIT EOS4 (with Cablelabel PUR and Flexiprint)



FLEXIMARK® THERMAL TRANSFER KIT EOS4 ORG (with organized shrink tube)



FLEXIMARK® THERMAL TRANSFER KIT EOS4 PUR (with Cablelabel PUR)



General description:

- Cost efficient kit with durable marking for cables in industrial environment
- Thermal transfer printer CAB EOS4 is delivered together with FLEXIMARK® Software without extra charge
- Smart and flexible thermal transfer printer helps you to quickly produce your own marking when you need it
- FLEXIMARK® Cablelabel PUR is a halogen free, flame retardant, flexible and durable cable marking
- FLEXIMARK® Cable marking on a roll helps you keep your marking sorted and easy to handle

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83259896EN Version: 03	Page 1 of 3
--	---------------------------------------	-------------

83259896	DATA SHEET	
Valid from: 18.09.2018	FLEXIMARK® THERMAL TRANSFER KIT	

Technical data Thermal transfer printer CAB EOS4:

- Dimension HxWxD: 245x412x264mm
- Maximum printing speed: 125mm/s
- Maximum printing width (Material): 106mm
- Maximum printing length* (Material): 1016mm
- Weight: 5kg
- Maximum label roll diameter Ø: 210mm
- Minimum core diameter Ø: 38mm

*Maximum printing length is the maximum length of the material the printer can print in once sequence.

Technical data FLEXIMARK® Organized shrink tube:

- Colour: yellow
- Material: Polyolefin, halogen free
- Shrink ratio: 2:1
- Temperature area: -30 to +105°C
- Shrink temperature: Minimum +90°C

Technical data FLEXIMARK® Cablelabel PUR:

- Colour: yellow
- Material: PUR, Thermoplastic, polyether, polyurethane, halogen free, hydrolysis and micro organism resistant
- Temperature area: -25 to +80°C
- Approval raw material: UL94-V0
- Approval yellow material: UV-resistant

Technical data FLEXIMARK® Flexiprint wire marking:

- Colour: yellow
- Material: Polyester, halogen free
- Temperature range: -40 to +125°C

Advantages:

- Cost efficient kit for printing your own cable marking
- Durable marking for industrial environment
- Roll of marking gives you a better overview and helps you keep your marking sorted at all time
- A thermal transfer printer with high user comfort
- Thermal transfer printing method increases smudge, scratch resistance and resistance to oils and chemicals.
- Flexible and self-extinguishing polyolefin tubing
- Durable cable marking with fast and flexible printing

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83259896EN Version: 03	Page 2 of 3
--	---------------------------------------	-------------

83259896	DATA SHEET	
Valid from: 18.09.2018	FLEXIMARK® THERMAL TRANSFER KIT	

FLEXIMARK® THERMAL TRANSFER KIT:

Part no.	Article designation	Included FLEXIMARK® Marking	PU
83259896	FLEXIMARK Thermal transfer kit EOS4 ORG	1 roll organized shrink tube yellow	1
83259895	FLEXIMARK Thermal transfer kit EOS4 PUR	2 rolls Cablelabel PUR yellow	1
83259897	FLEXIMARK Thermal transfer kit EOS4	1 roll Cablelabel PUR yellow 1 roll Flexiprint TF1 yellow	1



Content:

FLEXIMARK® THERMAL TRANSFER KIT ORG:

Part no.	Article designation	Article details	Packaging unit	Content (unit)
83259598	Thermoprint EOS4/300	Thermal transfer printer CAB EOS4	1pcs	1 printer
83260206	Ribbon FTI-X 60x300 BK	Black ribbon	1 roll	300m
83260227	O.shr 4.8/2.4-12.5(4)0-halYE	Yellow organized shrink tube	1roll	4000 labels /roll
83251080	FLEXIMARK Software 10	Software for printing your own marking	1pcs	1 software

USB cable included in the package / all included articles can be reordered



Content:

FLEXIMARK® THERMAL TRANSFER KIT PUR:

Part no.	Article designation	Article details	Packaging unit	Content (unit)
83259598	Thermoprint EOS4/300	Thermal transfer printer CAB EOS4	1pcs	1 printer
83260201	Ribbon FTI-Y 60x360 BK	Black ribbon	1 roll	360m
83260191	Cablelabel PUR 60x10 mm YE	Cablelabel PUR marking	2 rolls	1000 labels /roll
83251080	FLEXIMARK Software 10	Software for printing your own marking	1pcs	1 software

USB cable included in the package / Cable ties are not included in the

kit / all included articles can be reordered



Content:

FLEXIMARK® THERMAL TRANSFER KIT EOS4:

Part no.	Article designation	Article details	Packaging unit	Content (unit)
83259598	Thermoprint EOS4/300	Thermal transfer printer CAB EOS4	1st	1 printer
83260201	Ribbon FTI-Y 60x360 BK	Black ribbon	1 roll	360m
83260191	Cablelabel PUR 60x10 mm YE	Cablelabel PUR marking	1 roll	1000 labels/roll
83254378	Flexiprint TF 0.75-1.5YE	Flexiprint wire marking	1 roll	2000 labels/roll
83251080	FLEXIMARK Software 10	Software for printing your own marking	1pcs	1 software

Foot note:

Photographs are not to scale and do not represent detailed images of the respective products.

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83259896EN Version: 03	Page 3 of 3
--	---------------------------------------	-------------