

	DATA SHEET	
Valid from: 02.05.2019	FLEXIMARK® Character holders PTE	

Cable and component marking on site.
 Indoor and outdoor environment.
 Used together with different FLEXIMARK® Marking system.
 For cable marking mounted with plastic cable ties.
 For component marking mounted with screw.



Technical data

Material PTE:	Polyethylene, halogen free
Temperature range:	-75°C up to +80°C
Resistance:	UV-resistant
Recommended storage:	Cool and dry in original packaging

Mounting:

FLEXIMARK® Character holders are be used for both cable and component marking. You simply punch the holes for cable ties or screws as you need them.

Other product data:

ETIM Classification:	EC001288
----------------------	----------

Advantages:

Flexible and durable marking when you need it.
 Easy marking on site together with 3M™ DYMO™ Industrial marking labels and different FLEXIMARK® Marking systems.
 Halogen free material.
 Cable and component marking for indoor and outdoor.
 Mounted with one or two cable ties for cable marking and with screws for component marking.

Delivery:


Delivered in different lengths. Character holders with a length of 5m and over are delivered in a box for easier handling.

Creator: Fleximark/LR	Document: DB83251060EN Version: 02	Page 1 of 3
-----------------------	---------------------------------------	-------------

	DATA SHEET	
Valid from: 02.05.2019	FLEXIMARK® Character holders PTE	

Product data:

E-number	LAPP Part no.	Article designation	Width (mm)	Length (mm)	Adhesive	Content (unit)	PU
2989392	83253014	PTE 6-285	6	285	No	10	1
2989394	83253012	PTE 6-1000	6	1000	No	10	1
2942227	83259960	PTE 6-15m	6	15 m	No	1	1
2989402	83252081	PTE 9.5-285	9,5	285	No	10	1
2989404	83252084	PTE 9.5-1000	9,5	1000	No	10	1
2942228	83259961	PTE 9.5-15m	9,5	15 m	No	1	1
2989412	83252028	PTE 12-285	12	285	No	10	1
2989414	83252027	PTE 12-1000	12	1000	No	10	1
2972177	83259952	PTE 12-10m	12	10 m	No	1	1
2989422	83251060	PTE 19-285	19	285	No	10	1
2989424	83251061	PTE 19-1000	19	1000	No	10	1
2972178	83259953	PTE 19-5m	19	5 m	No	1	1
2989432	83252508	PTE 25-285	25	285	No	10	1
2989434	83252510	PTE 25-1000	25	1000	No	10	1
2972179	83259954	PTE 25-5m	25	5 m	No	1	1




Creator: Fleximark/LR	Document: DB83251060EN Version: 02	Page 2 of 3
-----------------------	---------------------------------------	-------------

	DATA SHEET	
Valid from: 02.05.2019	FLEXIMARK® Character holders PTE	

Related products

With the FLEXIMARK® Plier for Character holders you can both cut your holders into desired length, punch both holes for cable tie mounting and center hole for screw mounting.



FLEXIMARK® Character holders are used together with 3M™ DYMO™ Industrial marking labels (vinyl, polyester, glue-free, nylon) or different FLEXIMARK® Marking systems. All of the related products are available in our assortment.

Following FLEXIMARK® Marking systems or solutions are recommended for FLEXIMARK® Character holders PTE and PTES:

Article no.	Article description	Recommended FLEXIMARK® Marking systems
83253014	PTE 6-285	3M™ DYMO™ Marking label 6mm
83253012	PTE 6-1000	3M™ DYMO™ Marking label 6mm
83259950	PTE 6-10m	3M™ DYMO™ Marking label 6mm
83252081	PTE 9.5-285	3M™ DYMO™ Marking label 9,5mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 9,5mm
83252084	PTE 9.5-1000	3M™ DYMO™ Marking label 9,5mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 9,5mm
83259951	PTE 9.5-10m	3M™ DYMO™ Marking label 9,5mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 9,5mm
83252028	PTE 12-285	3M™ DYMO™ Marking label 12mm
83252027	PTE 12-1000	3M™ DYMO™ Marking label 12mm
83259952	PTE 12-10m	3M™ DYMO™ Marking label 12mm
83251060	PTE 19-285	3M™ DYMO™ Marking label 19mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 19mm
83251061	PTE 19-1000	3M™ DYMO™ Marking label 19mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 19mm
83259953	PTE 19-5m	3M™ DYMO™ Marking label 19mm FLEXIMARK® MINI Marking system FLEXIMARK® Flexilabel 19mm
83252508	PTE 25-285	3M™ DYMO™ Marking label 25mm
83252510	PTE 25-1000	3M™ DYMO™ Marking label 25mm
83259954	PTE 25-5m	3M™ DYMO™ Marking label 25mm

Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83251060EN Version: 02	Page 3 of 3
-----------------------	---------------------------------------	-------------