

AV1000 Gigabit Powerline Wi-Fi Extender

Model: MP510 KIT


// Highlights

- Eliminate Wi-Fi Dead-Zones – Extend 300 Mbps Wi-Fi via Your Home's Wiring
- 1000 Mbps Powerline Transfer Rate – Fast and Stable Transmissions with Advanced HomePlug AV2
- Super-Fast Wired Connection – A Gigabit Port for PCs, IPTVs, and Game Consoles
- 4K Streaming Mate – Extend Wi-Fi to Every Corner of Your Home



// Applications


Extend Wi-Fi Everywhere Via Your Home's Electrical Circuit



// Features


High-Speed Powerline Transmissions

Equipped with advanced HomePlug AV2 technology, the ultra-fast data transmission rate reaches up to 1000 Mbps for a high-quality connection from any of your outlets.




Plug and Play

Without complex wiring and configuration, immediately extend your network as soon as you connect one MP500 to your router and plug the MP510 into an outlet.




Unify Your Wi-Fi Networks

Press the Wi-Fi Clone Button on the MP510 to copy the SSID and password from your router and create a single, unified Wi-Fi network throughout your home. Any setting changes will be automatically applied to the entire Powerline network.




Easy Expansion

If a typical two-pack kit doesn't meet all your networking needs, simply add more Powerline adapters to expand your network to any room.



// Connections

No complex wiring and configuration, just Plug and Play



// Specifications

Physical Specifications

Plug Type: EU

Standards and Protocols:

HomePlug AV2, IEEE 802.3, IEEE 802.3u, IEEE802.11b/g/n

Power Consumption:

MP510: Maximum: 6.28W, Typical: 4.29W

MP500: Maximum: 2.87W, Typical: 2.35W, Standby: 0.64W

Range: Up to 300 meters over an existing electrical circuit

Interface: 1x Gigabit Port


Button: Pair/Reset Button

LED Indicator: Power

Dimensions (L x W x H):

MP510: 112 × 84.7 × 39 mm

MP500: 101 × 60 × 36 mm



// Specifications

Software Specifications

Modulation Technology: OFDM (PLC)

Security:

Wireless:

WEP, WPA/WPA2-Personal, WPA2/WPA3-Personal Encryption;

Powerline: 128-bit AES Encryption

Compatibility:

Compatible with all routers and HomePlug AV/AV2 powerline adapters

Other Specifications

Certification: CE, RoHS

Package Contents

- AV1000 Gigabit Powerline Wi-Fi Kit

- 1× MP510

- 1× MP500

- Quick Installation Guide

- RJ45 Ethernet Cables

System Requirements:

Windows 2000/XP/2003/Vista, Windows 7/8/8.1/10, Mac, Linux

Environment

- Operating Temperature: 0°C~40°C (32°F~104°F)

- Operating Humidity: 10%~90% Non-Condensing

- Storage Humidity: 5%~90% Non-Condensing

Specifications are subject to change without notice. MERCUSYS is a registered trademark of MERCUSYS TECHNOLOGIES CO., LTD. Other brands and product names are trademarks or registered trademarks of their respective holders. Copyright © 2020 MERCUSYS TECHNOLOGIES CO., LTD. All rights reserved.

*Maximum Powerline signal rates are the physical rates derived from HomePlug AV/AV2 specifications. Actual Powerline data throughput and Powerline range are not guaranteed and will vary as a result of network conditions and environmental factors, including electrical interference, volume of traffic and network overhead, AFCI circuit breaker, and Powerline being on a separate circuit.

*Maximum wireless signal rates are the physical rates derived from IEEE Standard 802.11 specifications. Actual wireless data throughput and wireless coverage are not guaranteed and will vary as a result of network conditions, client limitations, and environmental factors, including building materials, obstacles, volume and density of traffic, and client location.

*Compatible with all HomePlug AV and AV2 Standard Powerline adapters. This product may not be compatible with routers or gateways with firmware that have been altered, are based on open source programs, or are non-standard or outdated.

*Use of WPA3 requires clients to also support WPA3. Further software upgrades for feature availability may be required.