

Hook-and-Loop Pads with Self-Adhesive Back Item-No.: 25CA652 ... 25CA688



These self-adhesive hook and loop pads are ideal for fixing tasks on suitable surfaces. The reliable 3M adhesive surface ensures a stable hold and a long service life. It is important that the surfaces are smooth and clean so that the adhesive film can develop its full holding power.

Basic strength is achieved shortly after application - final strength is achieved after a maximum of 24 hours. The black or white design can be unrestricted and inconspicuous in many usages.

Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: Black, White • RoHS compliant, REACH compliant • Content: Set of 10, 30 or 40 pcs.

Part-No.	Description	Color	Dimensions	Content	EAN/GTIN
25CA652	Hook & Loop Pad rectangular	Black	25 x 25 mm	10 pcs.	4262511624373
25CA653	Hook & Loop Pad rectangular	Black	25 x 50 mm	10 pcs.	4262511624380
25CA654	Hook & Loop Pad rectangular	Black	25 x 100 mm	10 pcs.	4262511624397
25CA655	Hook & Loop Pad rectangular	Black	40 x 40 mm	10 pcs.	4262511624403
25CA656	Hook & Loop Pad rectangular	Black	50 x 50 mm	10 pcs.	4262511624410
25CA657	Hook & Loop Pad rectangular	Black	60 x 60 mm	10 pcs.	4262511624427
25CA658	Hook & Loop Pad rectangular	Black	50 x 100 mm	10 pcs.	4262511624434
25CA659	Hook & Loop Pad rectangular	Black	100 x 200 mm	10 pcs.	4262511624441
25CA660	Hook & Loop Pad round	Black	Ø 25 mm	10 pcs.	4262511624458
25CA661	Hook & Loop Pad round	Black	Ø 40 mm	10 pcs.	4262511624465
25CA662	Hook & Loop Pad round	Black	Ø 50 mm	10 pcs.	4262511624472
25CA663	Hook & Loop Pad round	Black	Ø 60 mm	10 pcs.	4262511624489
25CA664	Hook & Loop Pad round	Black	Ø 100 mm	10 pcs.	4262511624496
25CA665	Hook & Loop Pad-Set rectangular*	Black	25 x 25 mm, 25 x 50 mm, 25 x 100 mm, 50 x 100 mm	40 pcs.	4262511624502
25CA666	Hook & Loop Pad-Set rectangular*	Black	25 x 25 mm, 40 x 40 mm, 50 x 50 mm, 60 x 60 mm	40 pcs.	4262511624519
25CA667	Hook & Loop Pad-Set various*	Black	25 x 25 mm, 50 x 50 mm, Ø 25 mm, Ø 50 mm	40 pcs.	4262511624526
25CA668	Hook & Loop Pad-Set various*	Black	50 x 50 mm, 50 x 100 mm, Ø 50 mm	30 pcs.	4262511624533
25CA669	Hook & Loop Pad-Set round*	Black	Ø 25 mm, Ø 50 mm, Ø 100 mm	30 pcs.	4262511624540
25CA670	Hook & Loop Pad rectangular	White	25 x 25 mm	10 pcs.	4262511624557
25CA671	Hook & Loop Pad rectangular	White	25 x 50 mm	10 pcs.	4262511624564
25CA672	Hook & Loop Pad rectangular	White	25 x 100 mm	10 pcs.	4262511624571
25CA673	Hook & Loop Pad rectangular	White	40 x 40 mm	10 pcs.	4262511624588
25CA674	Hook & Loop Pad rectangular	White	50 x 50 mm	10 pcs.	4262511624595
25CA675	Hook & Loop Pad rectangular	White	60 x 60 mm	10 pcs.	4262511624601
25CA676	Hook & Loop Pad rectangular	White	50 x 100 mm	10 pcs.	4262511624618
25CA677	Hook & Loop Pad rectangular	White	100 x 200 mm	10 pcs.	4262511624625
25CA678	Hook & Loop Pad round	White	Ø 25 mm	10 pcs.	4262511624632
25CA679	Hook & Loop Pad round	White	Ø 40 mm	10 pcs.	4262511624649
25CA680	Hook & Loop Pad round	White	Ø 50 mm	10 pcs.	4262511624656
25CA681	Hook & Loop Pad round	White	Ø 60 mm	10 pcs.	4262511624663
25CA682	Hook & Loop Pad round	White	Ø 100 mm	10 pcs.	4262511624670
25CA683	Hook & Loop Pad-Set rectangular*	White	25 x 25 mm, 25 x 50 mm, 25 x 100 mm, 50 x 100 mm	40 pcs.	4262511624687
25CA684	Hook & Loop Pad-Set rectangular*	White	25 x 25 mm, 40 x 40 mm, 50 x 50 mm, 60 x 60 mm	40 pcs.	4262511624694
25CA685	Hook & Loop Pad-Set various*	White	25 x 25 mm, 50 x 50 mm, Ø 25 mm, Ø 50 mm	40 pcs.	4262511624700
25CA686	Hook & Loop Pad-Set various*	White	50 x 50 mm, 50 x 100 mm, Ø 50 mm	30 pcs.	4262511624717
25CA687	Hook & Loop Pad-Set round*	White	Ø 25 mm, Ø 50 mm, Ø 100 mm	30 pcs.	4262511624724
25CA688	Hook & Loop Pad-Set various	Black + White	40 x 40 mm, Ø 40 mm (10x / color)	40 pcs.	4262511624731

* 10 x per dimension