

Technaxx® user manual

Car Light Beacon 12V TX-349

Before using the appliance for the first time, please read the instructions for use and safety information carefully.

Keep this user manual for future reference or product sharing carefully. Do the same with the original accessories for this product. In case of warranty, please contact the dealer or the store where you bought this product.

Features

- Use during vehicle breakdowns or emergencies
- 360° LED for high visibility
- 12V Power Adapter
- Magnetic and suction cup mounting

Declaration of Conformity

CE Technaxx Deutschland GmbH & Co. KG hereby declares that the equipment type TX-349 Prod. ID.:5334 is in compliance with Directive 2014/30/EU and ECE R10 & ECE R65. The full text of the EU Declaration of Conformity is available at the following internet address: www.technaxx.de/reseller

Disposal



Disposal of the packaging. Sort packaging materials by type upon disposal. Dispose of cardboard and paperboard in the waste paper. Foils should be submitted for recyclables collection.



Disposing of old equipment (Applies in the European Union and other European countries with separate collection (collection of recyclable materials) Old equipment must not be disposed of with household waste! Every consumer is required by law to dispose of old devices that can no longer be used separately from household waste, e.g. at a collection point in his or her municipality or district. This ensures that the old devices are properly recycled and that negative effects on the environment are avoided. For this reason, electrical devices are marked with the symbol shown here.

Technical specification

Power	18 W
Power Source	12 V Car Adapter (Cigarette Lighter Plug)
Wire	3 m
LED	10 LED
Light Mode	Flashing (double / sextuple) / Rotating
Protection Class	IP 65
Certifications	E9*10R06/00*22834*00 (R10) E9*65R00/10*6652*00 (R65)
Class	T1
Working temperature	-10 to +50°C
Weight / Dimension	555 g / 14 cm x 14 cm x 13.5 cm
Package contents	Light Beacon 12V TX-349, user manual

Product Overview



How to use

This high-visibility device is designed to alert other drivers to your vehicle's presence in case of a breakdown or emergency. It must be mounted on the roof of your vehicle to enhance visibility and ensure your safety on the road.



Important Safety Information

- This device is not a substitute for emergency assistance. Always call emergency services if necessary.
- Only use the light in emergency situations to avoid distraction to other drivers.
- Ensure the light is securely mounted before use to prevent any accidents.
- The warning light is intended for temporary use.
- Do not use the light while driving; it is for use when your vehicle is stationary.
- Keep the device and adapter out of reach of children.
- The light is water-resistant but not waterproof. Avoid use in heavy rain or conditions where the device may be submerged in water.

Powering the Light

- Plug the 12V adapter into your vehicle's cigarette lighter socket.
 - The light will automatically turn on once it is powered.
- If the light does not turn on, make sure your vehicle's ignition is on or in accessory mode.


Operation

- The warning light will flash in a bright, attention-grabbing pattern. Ensure the light is visible to approaching drivers.
- Do not use the light while driving. Only activate the warning light when your vehicle is stationary.
- Place the light in case of an emergency only on top of your car.

Modes

The light features 3 different modes (3):

- Double flash mode - 1
- Sixtuple flash mode - 2
- Rotating mode - 3



To switch between the modes, unscrew the top yellow cover and move the switch to the 'ON' position as required. Screw the cover back onto the lamp. **Important:** Only set one mode to ON at a time, otherwise the lamp will distort the light pattern.

Note: Regulations of light pattern may vary depending on the country in which the lamp is used.

Turning Off the Light

- To turn off the light, unplug the adapter from the vehicle's cigarette lighter socket.
- Carefully remove the light from the roof of your vehicle.

Support

Service phone No. for technical support: **01805 012643**

(14 cent/minute from German fixed-line and 42 cent/minute from mobile networks). Free Email: **support@technaxx.de**

The support hotline is available Mon-Fri from 9 am to 1 pm & 2 pm to 5 pm.

Cleaning and maintenance

- Clean the equipment regularly with a moist cloth. Do not use cleaning agents or solvents.
- Ensure that no water can seep into the plugs. The ingress of water into an electric device increases the risk of an electric shock or damage of the device.

Made in China

Distributed by:
Technaxx Deutschland GmbH & Co. KG
Konrad-Zuse-Ring 16-18,
61137 Schöneck, Germany