

D Hartmetall-Frässtifte,
Walzenrund

E Tungsten carbide rotary burrs,
ball nose


ES Puntas de avellanado de metal
duro esferocilindricas



INOX



Aluminium
Aluminium
Aluminio




DIN MY



Diamant
Diamond
Diamante




DIN MX



DIN
WRC

ISO
C



INOX

Herausragende Fräsleistung
bei Edelstahl/Niro

Outstanding milling
performance in stainless
steel

Rendimiento de fresado
excelente en acero inoxidable/
acero niro

Einzelverpackung
Single packing
Embalaje individual



* Einzelverpackung mit SB
Single packaging with tag
Embalaje individual con gancho
para autoservicio



d1	d2	l1	l2	Code 7790	Code 7798	Code 7792	Code 7793		
mm	mm	mm	mm	Art.-Nr.	Art.-Nr.	Art.-Nr.	Art.-Nr.		
3,00	3,00	38	14				0779303103100		
3,00	3,00	50	14				0779303203100		
4,00	3,00	40	10				0779303104100		
4,00	6,00	50	14				0779306104100		
5,00	3,00	42	12						
6,00	3,00	43	14				0779303106100		
6,00	6,00	50	14	0779006106100		0779206106100	0779306106100		
6,00	6,00	150	16				0779306206100		
8,00	6,00	65	20	0779006108100	0779806108100	0779206108100	0779306108100		
10,00	6,00	65	20	0779006110100	0779806110100	0779206110100	0779306110100		
10,00	6,00	70	25						
10,00	6,00	150	20						
12,00	6,00	70	25	0779006112100	0779806112100	0779206112100	0779306112100		
12,00	6,00	150	25						
12,00	8,00	70	25						
16,00	6,00	70	25						
20,00	6,00	70	25				0779306116100		





DIN MX



SPECIAL STEEL

Nähere Informationen zu den einzelnen Zahnungen siehe Seite 261.

Detailed information about the different cuts see on page 261.

Consulte en la página 261 información más detallada sobre todos los dentados.

SPECIAL STEEL

Aggressive Geometrie – hoher Materialabtrag

Aggressive geometry – high chip removal

Geometría agresiva – alta remoción de material

							
d1	d2	l1	l2	Code 7794 Art.-Nr.	Code 7796 Art.-Nr.	Code 7797 Art.-Nr.	Code 7799 Art.-Nr.
mm	mm	mm	mm				
3,00	3,00	38	14	0779403103100	0779603103100	0779703103100	
3,00	3,00	50	14		0779603203100		
4,00	3,00	40	10	0779403104100	0779603104100		
4,00	6,00	50	14		0779606104100		
5,00	3,00	42	12	0779403105100			
6,00	3,00	43	14	0779403106100	0779603106100		
6,00	6,00	50	14	0779406106100		0779706106100	0779906106100
6,00	6,00	150	16	0779406206100	0779606206100		
8,00	6,00	65	20	0779406108100	0779606108100	0779706108100	0779906108100
10,00	6,00	65	20	0779406110100	0779606110100 *	0779706110100	0779906110100
10,00	6,00	70	25		0779606310100		
10,00	6,00	150	20	0779406210100			
12,00	6,00	70	25	0779406112100	0779606112100 *	0779706112100	0779906112100
12,00	6,00	150	25	0779406212100			
12,00	8,00	70	25		0779608112100		
16,00	6,00	70	25	0779406116100	0779606116100		
20,00	6,00	70	25	0779406120100			



Hartmetall Werkzeuge
Tungsten carbide tools
herramientas de metal duro

