

The **NOMAD AIR** is a portable air compressor that packs power and versatility into an ultra-compact design. Capable of reaching 10 bar pressure, it delivers precise and rapid air delivery for all your inflatable items: from sports equipment to car tyres. Designed to be a truly multifunctional system, it incorporates a high-capacity lithium battery that also serves as both an external power supply, and an auxiliary light, offering a 3-in-1 solution that's on hand whenever you need it.

10 BARS OF PRESSURE FOR ALL INFLATION APPLICATIONS

- Delivering up to 10 bar (150 PSI), the NOMAD AIR allows for **rapid inflation** (30 l/min) of all pneumatic equipment.
- Equipped with a 22 mm diameter cylinder, it minimizes the risk of overheating during repeated high-pressure inflation.
- Its integrated battery provides sufficient power for successive uses, **ensuring reliable, consistent, and long-lasting inflation.**

	Pressure	Inflation time from 0 to the required pressure	Number of inflations per charge from 0 to the required pressure
Car tyre 195/60R15	2.5 bars	5 min	x 6
Racing bicycle tyre	8 bars	1 min	x 20
Basketball	0.6 bars	40 s	x 100

DESIGNED TO GO WITH YOU WHEREVER YOU GO

- **Ultra-lightweight** (610 g) and **compact**, it can be carried with you every day and fits easily into a backpack or glove compartment.
- The **dedicated carrying case** protects the compressor on the move and provides convenient storage for the charging cable and attachments.

SIMPLE, PRECISE, AND INDEPENDENT INFLATION

- The large digital display allows for at-a-glance pressure readings and intuitive adjustments.
- **Four preset inflation modes:** car, motorcycle, bicycle, and ball, plus a «Favorite» mode for quick and easy selection and setting of the desired pressure.
- Inflation **stops automatically** once the programmed pressure is reached, ensuring accuracy and safety.

ACCESSORIES FOR EVERY APPLICATION

Five different connectors allow the compressor to be connected to a wide range of equipment, even those with non-standard valves or connectors. The NOMAD AIR can inflate air mattresses, rubber-rings, and many other items.

A MULTIFUNCTIONAL TOOL

- **Auxiliary light** with 3 lighting modes (normal, SOS, strobe).
- It's USB-A 5V - 2.1A output port means you can also **use it to charge** your smartphone, tablet, and other electronic devices.



Supplied with accessories:



Case / bag
for transport



Charging cable
Type C / Type C



Nozzles / tips
for inflation

Optional charger unit



087132 67 W USB charger



087101 15 W USB charger

087354 15 W USB charger

BATTERY			COMPRESSOR		INPUT / OUTPUT		DIMENSIONS	
LITHIUM Battery			Maximum pressure	Air flow rate	INPUT	OUTPUT	cm	kg
Capacity per cell	Type	Full charge						
2.5 Ah 27.75 Wh	LiCoO ₂	2h15	10 bars 150 PSI	30 l/min	SB-C: 5V - 2A	1 USB-A: 5V - 2.1 A	6.4 x 5.65 x 17.55	0.61