






# DATASHEET

## EMC Cable retaining clip


### Overview

| Item no. 3758726 | Item no. 3758727 |
|---|---|
|  |  |
| **Item no. 3758728** | **Item no. 3758729** |
|  |  |
| **Item no. 3758730** | **Item no. 3758731** |
|  |  |


Item no. 3758732




Item no. 3758733




Item no. 3758734




| | |
|---|---|
| Material | Galvanized 65Mn spring steel (Blue Zinc Plated) |
| Color | Silver |
| Operating conditions | -20 to +70 °C, 20 - 95 % RH |
| Storage conditions | -40 to +85 °C, 10 - 95 % RH |

All dimensions in mm

## Technical data

| Item no. | Clamping Ø (mm) | Mounting hole Ø (mm) | Panel thickness max. (mm) | Dimensions (L x W x H) (mm) | Weight (g) |
|---|---|---|---|---|---|
| 3758726 | 3 - 6 | 1 x 3.2 | 0.5 | 13.98 x 11 x 8 | 1.3 |
| 3758727 | 8 - 11 | 1 x 3.2 | 0.5 | 18.97 x 12 x 8 | 1.7 |
| 3758728 | 11 - 17 | 1 x 3.2 | 0.5 | 25.19 x 13.5 x 8 | 2.2 |
| 3758729 | 6 - 8 | 1 x 3.2 | 0.5 | 17.17 x 11 x 8 | 1.5 |
| 3758730 | 1.5 - 3 | 1 x 3.2 | 0.5 | 12.1 x 11 x 8 | 1.1 |
| 3758731 | 17 - 22 | 1 x 3.2 | 0.5 | 34.22 x 22 x 8 | 3.8 |
| 3758732 | 38 - 48 | 2 x 3.2 and 2 x 4.0 | 1 | 64.06 x 39.99 x 12 | 17.7 |
| 3758733 | 30 - 37 | 2 x 3.2 and 2 x 4.2 | 1 | 54.72 x 40 x 12 | 16.2 |
| 3758734 | 22 - 30 | 1 x 3.2 | 0.5 | 40.29 x 22 x 12 | 10 |

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.