


LogiLink®

USB-C Patterned Fabric Sync & Charge Cable

USB-C male to USB-C male, 1 m

Art. No.: **CU0480–CU0483**

Unique & Eye-catching Decorative Fabric Patterns

This premium USB-C cable supports fast charging and data syncing for USB-C smartphones and tablets. With its durable fabric braid and eye-catching pattern, it makes everyday charging more colorful, stylish, and fun.



Fabric Braided

60 W 3 A max.


480 Mbps

1 m Cable



CE UK CA

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.




Soft with Beautiful

Add color to every connection with LogiLink premium USB-C cable. With durable fabric braided pattern brings a stylish, playful look to everyday charging and transfers.



- 1 m cable convenient for daily use.



PD Fast Charging & Data Sync

With up to 60 W power (20 V/3 A), you can quickly charge up laptops, phones, tablets and more. Also support 480 Mbps data transfer rate.



Universal Compatibility


Designed for the latest USB-C smartphones, tablets and laptops, this cable ensures effortless connectivity across your device's ecosystem.

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.


Made in China

Specifications:

Connection 1	USB-C male
Connection 2	USB-C male
USB Standard	USB 2.0
Max. Data Transfer Rate	Up to 480 Mbps
Power Delivery	Up to 60 W
Max. Current Capacity	3 A
Thunderbolt 3/4 Compatible	Yes
Material	Aluminum alloy, nickel plated, cotton fabric braided cable




CU0480
Blue/Red
4052792085631



CU0481
Turquoise/Pink
4052792085648



CU0482
Blue/Yellow
4052792085655



CU0483
Yellow/Red
4052792085662

Package Contents:

» 1 x USB-C Cable
» 1 x User Manual

Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
CU0480	100 x 160 x 14 mm	0.038 kg	440 x 360 x 240 mm	100 pcs	5.2 kg
CU0481	100 x 160 x 14 mm	0.038 kg	440 x 360 x 240 mm	100 pcs	5.2 kg
CU0482	100 x 160 x 14 mm	0.038 kg	440 x 360 x 240 mm	100 pcs	5.2 kg
CU0483	100 x 160 x 14 mm	0.038 kg	440 x 360 x 240 mm	100 pcs	5.2 kg

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Made in China