





Gel Battery / Gel Batterie Eco Store

340265, 340266, 340267, 340268, 340269, 340270 • 05/2018

The new Active Power Battery supports you in all your projects. The advantage of this new gel battery is its high cycle resistance. The Phaesun Eco Store manages 500 cycles. The battery is completely sealed. In normal use, there is no gas formation. Since no additional ventilation is required, the batteries can be installed anywhere. They are ideal as a service battery and for cyclic applications. In addition, they can be recharged very quickly. The battery is also extremely vibration resistant, completely maintenance-free and can be stored for up to 9 months.

Die neue Active-Power Batterie unterstützt Sie bei all Ihren Vorhaben. Der Vorteil dieser neuen Gel Batterie ist ihre hohe Zyklusfestigkeit. Die Phaesun Eco Store schafft es auf 500 Zyklen. Damit macht diese Power Gel Batterie Ihrem Namen alle Ehre. Die Batterie ist komplett verschlossen, bei normaler Verwendung gibt es keine Gasbildung. Da keine zusätzliche Belüftung erforderlich ist, können die Batterien überall installiert werden. Sie eignen sich ideal als Service-Batterie und für zyklische Anwendungen. Zudem können sie sehr schnell wieder aufgeladen werden.



Technical Data	Technische Daten	Eco Store 70	Eco Store 90	Eco Store 100	Eco Store 140	Eco Store 165	Eco Store 235	
Nominal voltage	Nennspannung			12				
Capacity	Kapazität		VDC					
		Ah (C5)	50	70	75	105	130	180
		Ah (C20)	60	80	85	125	150	210
	Ah (C100)	70	90	100	140	165	235	
Dimensions	Abmessungen	278 x 175 x 190	353 x 175 x 190	352 x 171 x 236	345 x 175 x 290	513 x 223 x 223	518x273x242	
Weight	Gewicht	21	26	31	40	52	71	
Electrolyte density	Elektrolytdichte			1,28				
Electrolyte	Elektrolyt			Verdünnte Schwefelsäure in GEL-festgelegt diluted sulphuric acid fixed in gel				
Enclosure	Gehäuse			Graues Gehäuse PP Ventil-Stopfen grey enclosure PP vent plug				
Bottom lath	Bodenleiste			B1				
Separator	Separator			Microporöser Taschenseparator microporous pocket separator				
Terminal Type	Polausführung							
Terminal position	Anschlussposition							
Degassing	Entgasung			Innere Gas-Rekombination internal gas recombination				
Delivery status	Auslieferungszustand			Gefüllt und geladen verschlossen Postversand möglich filled and charged sealed postal delivery possible				
Article No.	Artikel Nr.	340265	340266	340267	340268	340269	340270	