

APP CONTROLLED 2.0MP 1080P HD
PAN/TILT INDOOR WIFI IP CAMERA



1920x1080
1080P

WiFi (2.4G network)

Micro SD storage
max. 128 GB (card **not** incl.)



Download the free
Caliber smart home app:



HWC 202PT



Hacker proof



Multi accessible



8 714505 046518



- Wireless indoor 1080P HD camera
- Free "Caliber SMART HOME" app
- 1/3" Lens H.264 CMOS 2.0 MP
- Night vision (approx. 10m • high power IR LED lights)
- Connect through WiFi (WiFi 2.4G network)
- Supports a micro SD card storage (up to 128GB)
- Record function with loop recording
- Pan/Tilt function (Pan: 0~350°/ Tilt: -75~75°)
- Motion detection (automatic record, photo and alarm)
- Trigger for scenario's (E.G: turn lights-ON via smart socket, when motion is detected)
- Built-in microphone and speaker for two way audio (intercom)
- Power supply: 100V-240V AC 50/60HZ (wall adapter with 2m power cord included)
- Smart Home - powered by Tuya
- Works with Amazon Echo show
- GOOGLE Home Hub & Chromecast
- Accessible by multiple devices (phones, tablets, etc)
- Hacker proof
- APP works with any internet connection
- Dimensions: 58mm (L) x 64mm (W) x 68mm (H) (WiFi or mobile data)



- Caméra HD 1080P intérieure sans fil
- Application gratuite « Caliber SMART HOME »
- Objectif 1/3 po H.264 CMOS 2.0 MP
- Vision nocturne (environ 10 m • LED IR haute puissance)
- Connexion via WiFi (réseau WiFi 2.4G)
- Prend en charge un stockage de carte micro SD (jusqu'à 128 Go)
- Fonction d'enregistrement en boucle
- Fonction Pan/Tilt (Pan: Inclinaison 0~350°/ -75~75°)
- Détection de mouvement (enregistrement, photo et alarme automatiques)
- Microphone et haut-parleur intégrés pour l'audio bidirectionnel (intercom)
- Dimensions: 58 mm (L) x 64 mm (l) x 68 mm (H)
- Alimentation : 100V-240V AC 50 / 60HZ (adaptateur mural avec câble d'alimentation de 2m inclus)
- Smart Home - optimisé par Tuya
- Fonctionne avec Amazon Echo Show
- GOOGLE Home Hub & Chromecast
- Comptaible avec plusieurs périphériques (téléphones, tablettes, etc.)
- Anti-piratage
- L'application fonctionne avec toute connexion Internet (WiFi ou données cellulaires)



Remote controlled
Pan/Tilt function



100V-240V wall adapter
(2m USB-to-Mirco USB cable incl.)

CALIBER SMART HOME
- LIVING IN COMFORT -

CALIBERSMARTHOME.COM
FOR DEMO'S & INSTRUCTIONS

This product requires a WiFi 2.4G network
and a smart-phone/tablet

Wifi Freq range: 2402-2480 Mhz,
Max e.r.p.: <100mW/20dBm

Tuya word mark and logos are registered trademarks
owned by Tuya, Inc. and any use of such marks
by Caliber Europe BV is under license. Other
trademarks and trade names are those of their
respective owners.

CALIBER EUROPE BV

Kortakker 10 • 4264 AE Veen
The Netherlands • Tel: +31 416-699 000



www.caliber.nl