

APP CONTROLLED 2.0MP 1080P HD
OUTDOOR WIFI IP CAMERA



1920x1080
1080P

WiFi (2.4G network)

8 GB internal storage
pre-installed



IP66
Water Resistant

HWC 401

Download the free
Caliber smart home app:



Hacker proof



Multi accessible



- Wireless outdoor 1080P HD camera
- Free "Caliber SMART HOME" app
- 1/3" Lens H.264 CMOS 2.0 MP
- Water resistant (IP66)
- Night vision (approx. 30m • 24 IR LED lights)
- Built-in IR-CUT filter, no color cast and better night vision
- Connect through WiFi (WiFi 2.4G network) or LAN
- 8 GB internal storage pre-installed (Micro SD)
- Record function with loop recording
- Metal housing
- Fully adjustable by a strong, metal ball joint
- Motion detection (automatic record, photo and alarm)
- Dimensions: 180mm (L) x 60mm (W) x 60mm (H)
- Power supply: 100V-240V AC 50/60HZ (wall adapter with 1.5m power cord incl.)
- Smart Home - powered by Tuya
- Accessible by multiple devices (phones, tablets, etc)
- Hacker proof
- APP works with any internet connection (WiFi or mobile data)



- Caméra extérieure HD 1080P sans fil
- Application gratuite « Caliber SMART HOME »
- Objectif 1/3 po H.264 CMOS 2.0 MP • Résistant à l'eau (IP66)
- Vision nocturne (environ 30m • 24 LED IR)
- Filtre IR-CUT intégré, aucune prédominance de couleur et une meilleure vision nocturne
- Connexion via WiFi (réseau WiFi 2.4G) ou LAN
- 8 Go de stockage interne pré-installés (Micro SD)
- Fonction d'enregistrement en boucle
- Boîtier métallique
- Entièrement réglable grâce à un solide support métallique orientable
- Détection de mouvement (enregistrement, photo et alarme automatiques)
- Dimensions: 180 mm (L) x 60 mm (l) x 60 mm (H)
- Alimentation : 100V-240V AC 50 / 60HZ (adaptateur mural avec câble d'alimentation de 1.5m inclus)
- Smart Home - optimisé par Tuya
- Comptaible avec plusieurs périphériques (téléphones, tablettes, etc.)
- Anti-piratage



8 714505 046488



Fully adjustable by a strong, metal ball joint



WiFi connected with adjustable antenna (wired LAN connection is available)

CALIBER SMART HOME
- LIVING IN COMFORT -

CALIBERSMARTHOME.COM
FOR DEMO'S & INSTRUCTIONS

- L'application fonctionne avec toute connexion Internet (WiFi ou données cellulaires)

This product requires a WiFi 2.4G network and a smart-phone/tablet

Wifi Freq range: 2402-2480 Mhz, Max e.r.p.: <100mW/20dBm

Tuya word mark and logos are registered trademarks owned by Tuya, Inc. and any use of such marks by Caliber Europe BV is under license. Other trademarks and trade names are those of their respective owners.

CALIBER EUROPE BV

Kortakker 10 • 4264 AE Veen
The Netherlands • Tel: +31 416-699 000



www.caliber.nl