



# CHARGING CABINET 20 NOTEBOOKS + RACK 1XU 19"

CABINET DE CHARGE 20 NOTEBOOKS  
+ 1 RACK 1XU 19"

UP TO  
**20**  
NOTEBOOK

  
**RACK**  
1xU 19"

  
**PREMIUM**  
SECURITY



RJ45 socket  
Prise RJ45




20 Notebook  
compartments  
20 Compartiments  
Notebook



3 points lock  
Fermeture 3 points

**FRONT**  
AVANT



RACK 1xU 19"  
RACK 1xU 19"



20 AC socket to  
supply notebooks  
20 prises secteur au dos  
pour alimenter les notebooks

**BACK**  
ARRIÈRE

**FOR NOTEBOOKS AND  
ELECTRONIC DEVICES**



20 Notebook Compartments  
Compartmentiments 20 notebook



20 notebook power sockets + 1 rack 1xU 19"  
20 alimentations pour notebook + 1 pour rack 1xU 19"



Rack 1xU 19"  
Rack 1xU 19"



AC power sockets



Rack 1xU 19"



Secure 3 point lock



Omni directional wheels + brakes

## CHARGING CABINET 20 NOTEBOOKS + 1 RACK 1xU 19"

- Capacity: up to 20 notebooks 15,6"
- Maximal notebook format : 29.8 x 39.5 x 3.6cm
- 1 x Rack 1xU 19"
- 20 AC socket to supply notebooks
- 1 AC socket to supply rack 1xU 19"
- 1 RJ45 external socket
- Protection against overvoltage
- 3 points lock door
- 4 omnidirectional wheels with tire studs & brakes
- External circuit breaker
- Securing anchor point for cable or chain

## CABINET DE CHARGE 20 NOTEBOOKS + 1 RACK 1xU 19"

- Capacité: jusqu'à 20 ordinateurs portables 15,6 "
- Format d'ordinateur portable maximal: 29,8 x 39,5 x 3,6 cm
- 1 x Rack 1xU 19"
- 20 prises secteur pour alimenter les ordinateurs portables
- 1 prise secteur pour alimenter le rack 1xU 19 "
- 1 prise RJ45 extérieure
- Protection contre les surtensions
- Porte de verrouillage 3 points
- 4 roues omnidirectionnelles avec crampons et freins pour pneus
- Disjoncteur externe
- Fixation du point d'ancrage pour câble ou chaîne

## TECHNICAL SPECIFICATIONS

PRODUCT NAME	CHARGING CABINET 20 NOTEBOOKS + RACK 19" - 1 U
REF - EAN	901973 - 3 56704 901973 0
SPECIFICATIONS	<ul style="list-style-type: none"> <li>• Capacity: up to 20 notebooks</li> <li>• 1x RACK 19" - 1 U</li> <li>• Input: 220-240V AC 50/60Hz -BA</li> <li>• Output: 5V DC 2.4A max /port</li> <li>220V-240V ~50/60Hz, 120W max</li> <li>• Color : Black</li> </ul>
CONTENTS	<ul style="list-style-type: none"> <li>1 x Charging Cabinet 20 notebooks</li> <li>1 x AC power cable</li> <li>1 x Key set</li> </ul>
COMPATIBILITY	Notebooks & electronic devices
MAX DEVICE COMPARTMENT SIZE Width x Height x Depth	15,6" notebook - 29.8 x 39.5 x 3.6cm
PRODUCT DIMENSIONS Width x Height x Depth	55,2 x 89 x 57,3 cm
PACKAGED DIMENSIONS Width x Height x Depth	68 x 107 x 77cm
PRODUCT WEIGHT	55 Kg
PACKAGED WEIGHT	89 Kg
PCB	1
COUNTRY OF ORIGIN	China
WARRANTY	3 years + 10 years metallic parts



Pictures submit to change / Photos non-contractuelles - All trademarks and registered trademarks are the property of their respective owners / Toutes les marques commerciales et marques commerciales déposées sont les propriétés de leurs détenteurs respectifs