

# ITEM SPECIFICATIONS



Date 15-08-2022  
 Buyer Michael Janssen  
 Assistent Haiyan Tan

## GENERAL

<b>Name</b>	<b>Convection heater 2000W</b>	Country of origin	China
<b>Description</b>	<b>Alpina thermostat 3heat</b>	HS code	8516299900000000
Item number	<b>53x20x38,5cm CB</b>		
Item no. Supplier	871125238005 CH-Y02		

## SIZE, WEIGHT, MATERIAL SPECIFICATIONS

Item Length * Width * Height	530x200x385mm	Item gross weight	2,660 kg
Item / material specs 1		Item nett weight	1,973 kg
Item / material specs 2			

## SINGLE PACKAGING SPECIFICATIONS

Sort single packaging	COLOURBOX	Length * Width * Height	576x133x400mm
Weight 1 (Glass)		Weight 5 (Bioplastic)	
Weight 2 (Aluminium)		Weight 6 (Carton)	500 g
Weight 3 (Metal)		Weight 7 (Wood)	
Weight 4 (Plastic)	52 g	Weight 8 (Other)	

## TRANSPORT PACKAGING SPECIFICATIONS

Quantity outercarton	1 pcs	Quantity innercarton	NO INNER CARTON
Outer Carton Length	582 mm	Inner Carton Length	582 mm
Outer Carton Width	135 mm	Inner Carton Width	135 mm
Outer Carton Height	395 mm	Inner Carton Height	395 mm
Outer Carton NettWeight	2,10 kg	Inner Carton Nett Weight	NO INNER CARTON
Outer Carton Gross Weight	2,67 kg	Inner Carton Gross Weight	NO INNER CARTON
Outer Carton CBM	0,031000	Inner Carton CBM	0,031000
Arrows up Y/N	N	Fragile Y/N	N
		Quantity 20FT	903 pcs
		Quantity 40FT	1.871 pcs
		Quantity 40HC	2.065 pcs

# ITEM SPECIFICATIONS

## LEGAL REQUIREMENTS

EU900 COO	Certificate of Origin
EU910 GSP A	GSP form A
EU920 Decl Fumi	Declaration gas free container
EU940 2001/95/EC GPSG	General Product Safety
EU930 Batch PACK	Batch number on gift box
EU970 1907/2006 Cd	Cadmium in plastic materials
EU980 94/62/EC Verp	Packaging and packaging waste
EU950 1907/2006 REACH SVHC	REACH regulation concerning SVHC
EU253 SCCP	Limitation of short chain chlorinated paraffins
EU897 BoM	Bill of Material
EU898 Doi	Declaration of Identity
EU899 Supl. DoC	Supplier Declaration of Conformity
EU010 2014/35/EU LVD	Low Voltage Directive
EU020 2009/125/EC ECO	Framework directive on environmental impact
EU050 2014/30/EU EMC	Directive for Electro Magnetical Compatibility
EU070 2011/65/EC ROHS	Directive for Reduction of Hazardous Substances
EU020 IMPL ECO	Implementation and labelling ECO design articles
EU001 GS MARK	Co-Licence for GS marking

## ADDITIONAL SPECIFICATIONS

### Specifications

**Colour : White + black**

**Material : Steel and plastic**

**Indicator light : Yes**

**Power cable length : 1.75m**

**Adjustable thermostat : Yes**

**Remote control : No**

**Adjustable height : No**

**Integrated handles : Yes**

**Input voltage : 220-240V~ 50Hz**

**Power source type : Mains powered**

**Plug type : Type C (CEE 7/17)**

**Suitable for rooms up to : 15m<sup>2</sup>**

**Heating element : Yes**

**Type of heater : Convection heater**

**Overheating protection : Yes**

**Suitable for bathroom : No**

**With wheels : No**

**Wall mounting : No**

**Frost-free position : No**

**Maximum power consumption : 2000W**

**Timer function : No**

**Item size: 53,5\*20\*38,5cm**

**Item weight : ca. 2500gr**

**Number of heating levels : 3 levels (750W-1250W-2000W)**

**Turbo function : No**

**GS license available : Yes Intertek**