



## Kunststoff-Spannzangen-Knöpfe mit matter Oberfläche




## Plastic Collet Knobs with mat-black finished surface Bouton en matière plastic

Drehknopf, Ausführung matt Collet knobs, Type dull										
Ø A	B	C	Ø d	Ø D	Ø E	F	G	schwarz black Art.-Nr.	grau grey Art.-Nr.	
12	14	7,5	3 3,2 4	-	-	-	5	<b>4307.3131</b> 4307.1131 <b>4307.4131</b>	4307.3141 4307.1141 4307.4141	
15	16	9,5	4 6 6,35	-	-	-	5	<b>4309.4131</b> <b>4309.6131</b> 4309.7131	4309.4141 4309.6141 4309.7141	
20	17	13	4 6 6,35	-	17	2,5	11	<b>4311.4131</b> <b>4311.6131</b> 4311.7131	4311.4141 4311.6141 4311.7141	
28	18,5	17	6 6,35	-	23	4,5	11	<b>4312.6131</b> 4312.7131	4312.6141 4312.7141	

Ø A	B	C	Ø d	Ø D	Ø E	F	G	schwarz black Art.-Nr.	grau grey Art.-Nr.
12	18	10,5	3 3,2 4	17	15	2,5	9	<b>4308.3131</b> 4308.1131 <b>4308.4131</b>	4308.3141 4308.1141 4308.4141
15	20	12	4 6 6,35	20	18	2,5	9	<b>4310.4131</b> <b>4310.6131</b> 4310.7131	4310.4141 4310.6141 4310.7141

## Abdeckkappe, flache Ausführung Oberfläche matt



## Caps, flat Design Mat surface

Strichanzeige Indicator Mark	Farbe Colour	Abdeckkappen passend zu Knopf-Durchmesser: A Caps fit to Knob-Diameter: A			
		Ø 12	Ø 15	Ø 20	Ø 28
		Art.-Nr.	Art.-Nr.	Art.-Nr.	Art.-Nr.
ohne/without	rot/red	<b>4307.0021</b>	<b>4309.0021</b>	<b>4311.0021</b>	<b>4312.0021</b>
ohne/without	schwarz/black	<b>4307.0031</b>	<b>4309.0031</b>	<b>4311.0031</b>	<b>4312.0031</b>
ohne/without	grau/grey	<b>4307.0041</b>	<b>4309.0041</b>	<b>4311.0041</b>	<b>4312.0041</b>
schwarz/black	rot/red	<b>4307.0121</b>	<b>4309.0121</b>	<b>4311.0121</b>	<b>4312.0121</b>
weiß/white	schwarz/black	<b>4307.0131</b>	<b>4309.0131</b>	<b>4311.0131</b>	<b>4312.0131</b>
schwarz/black	grau/grey	<b>4307.0141</b>	<b>4309.0141</b>	<b>4311.0141</b>	<b>4312.0141</b>

Abdeckplatten in Ausführung matt, bei Bedarf einsetzbar für Drehknöpfe blank.  
Caps in mat design, by requirement set in for turning knobs, bright.