

D Hartmetall-Frässtifte,
Spitzbogen

E Tungsten carbide rotary burrs,
arc pointed nose


ES Puntas de avellanado de metal
duro, angulares ojivales



INOX



2




4

Diamant
Diamond
Diamante




1A

Aluminium
Aluminium
Aluminio



3

DIN MY




6

DIN MX



DIN
SPG

ISO
G



INOX

Herausragende Fräsleistung
bei Edelstahl/Niro

Outstanding milling
performance in stainless
steel

Rendimiento de fresado
excelente en acero inoxidable/
acero niro

Einzelverpackung
Single packing
Embalaje individual



* Einzelverpackung mit SB
Single packaging with tag
Embalaje individual con gancho
para autoservicio



				0	1A	2	3
d1	d2	l1	l2	Code 7800 Art.-Nr.	Code 7808 Art.-Nr.		Code 7803 Art.-Nr.
mm	mm	mm	mm				
3,00	3,00	38	12				0780303103100
4,00	3,00	40	10				0780303104100
4,00	6,00	50	14				
6,00	3,00	43	13				0780303106100
6,00	6,00	50	16	0780006106100			0780306106100
8,00	6,00	65	20	0780006108100			0780306108100
NEW 10,00	6,00	65	20	0780006110100	0780806110100		0780306110100
12,00	6,00	70	25	0780006112100	0780806112100		0780306112100
12,00	6,00	75	25				
12,00	8,00	70	25				
16,00	6,00	75	30				0780306116100
16,00	8,00	75	30				





DIN MX



SPECIAL STEEL

Nähere Informationen zu den einzelnen Zahnungen siehe Seite 261.

Detailed information about the different cuts see on page 261.

Consulte en la página 261 información más detallada sobre todos los dentados.

SPECIAL STEEL

Aggressive Geometrie – hoher Materialabtrag

Aggressive geometry – high chip removal

Geometría agresiva – alta remoción de material

							
d1 mm	d2 mm	l1 mm	l2 mm	Code 7804 Art.-Nr.	Code 7806 Art.-Nr.	Code 7807 Art.-Nr.	Code 7809 Art.-Nr.
3,00	3,00	38	12	0780403103100	0780603103100	0780703103100	
4,00	3,00	40	10				
4,00	6,00	50	14		0780606104100		
6,00	3,00	43	13	0780403106100			
6,00	6,00	50	16	0780406106100	0780606106100 *	0780706106100	0780906106100
8,00	6,00	65	20	0780406108100	0780606108100		0780906108100
10,00	6,00	65	20	0780406110100	0780606110100	0780706110100	0780906110100
12,00	6,00	70	25	0780406112100	0780606112100 *	0780706112100	0780906112100
12,00	6,00	75	25		0780606212100		
12,00	8,00	70	25		0780608112100		
16,00	6,00	75	30	0780406116100	0780606116100		
16,00	8,00	75	30		0780608116100		



Hartmetall Werkzeuge
Tungsten carbide tools
herramientas de metal duro

