


Sehr geehrter Kunde, vielen Dank, dass Sie sich für dieses Qualitätsprodukt von kh-security entschieden haben. Bitte lesen Sie diese Bedienungsanleitung vor dem Gebrauch des Produkts sorgfältig durch.



- Übersicht:**
1. Handschlaufe
 2. Aluminium-Gehäuse
 3. drehbarer Ring
 4. Leuchte
 5. Endabdeckung mit Schalter
 6. USB-Anschluss zum Aufladen
 7. LED-Anzeige beim Aufladen

Merkmale des Alarm-Taschenlampe:

1. Die Taschenlampe ist mit einem akustischen Alarm ausgestattet, der einfach auf Knopfdruck aktiviert wird. Bei zweimaligem Drücken des Schalters [5] ertönt ein schriller, ca. 120dB lauter Alarmton, der Passanten in der Nähe aufmerksam macht und Angreifer abschrecken kann.
2. Die Taschenlampe ist mit neuester CREE-S3-LED-Technologie ausgestattet. Die LEDs haben eine Lebensdauer von bis zu 100.000 Stunden.
3. Das Gehäuse ist aus Aluminium hergestellt, das auch im Flugzeugbau verwendet wird.
4. Zudem wird die Oberfläche mit einem speziellen Verfahren behandelt, das das Gehäuse zusätzlich vor Abnutzung und Beschädigungen schützt.


Benutzung der Alarm-Taschenlampe:

1. Drücken Sie den Schalter am hinteren Ende der Taschenlampe [5], um die LED-Taschenlampe zu steuern. Die Taschenlampe verfügt über 3 verschiedene Modi: 100% Leuchtkraft, 30% Leuchtkraft, SOS-Signal.
2. Drücken Sie den Schalter wiederholt kurz, um in der folgenden Reihenfolge durch die Leuchtmodi zu wechseln: 100% - 30% - SOS-Signal - aus. Durch langes Drücken des Schalters schalten Sie die Taschenlampe sofort aus; egal, in welchem Leuchtmodus sie sich aktuell befindet.
3. Um Alarm auszulösen: Drücken Sie den Schalter am hinteren Ende der Taschenlampe zweimal schnell hintereinander. Der akustische Alarm ertönt und die LED beginnt zu blinken.
4. Um den integrierten Akku in der Taschenlampe aufzuladen, drehen Sie den Ring [3] im vorderen Bereich der Taschenlampe bis Sie den Anschluss für das mitgelieferte USB-Kabel sehen und schließen Sie das Kabel an den Anschluss an der Taschenlampe [6] und einen USB-Anschluss (Computer oder Steckernetzteil) an.
5. Während des Ladevorgangs leuchtet die LED-Anzeige [7] rot. Wenn die LED blau leuchtet ist der Ladevorgang abgeschlossen. Bitte drehen Sie nachdem Sie das USB-Kabel abgezogen haben den Ring wieder so, dass der USB-Anschluss [6] verdeckt ist. Dies schützt den Anschluss vor dem Eindringen von Wasser.

Technische Daten:

Art.Nr.	300150
Material	Aluminium
LED-Technologie	USA CREE XPG2-S3
Abmessungen	Ø31 x 98mm
Gewicht	99g
Leuchtmodi	100%, 30%, SOS-Signal
Leuchtkraft	100-300lm
Leuchtreichweite	ca. 30m
Alarmlautstärke	ca. 120dB
Batterie	1x 16340 (wiederaufladbar)
Laufzeit	bei 100% Licht: ca. 90 Minuten / bei 30% Licht: ca. 180 Minuten / bei Alarm: ca. 160 Minuten

Dear customer, thank you very much for choosing this quality product by kh-security. Please read this user manual carefully before using the product.



- overview:**
1. tail rope
 2. aviation aluminum body
 3. rotating ring
 4. buzzing
 5. back cover with on-off-switch
 6. USB charging port
 7. LED charging indicator

product features:

1. This flashlight comes with an integrated alarm siren that is very easy to use with the press of a button. When double pressing the on-off-switch, the piercing, approx. 120dB alarm starts instantly. The alarm signal can scare attackers away and summon help. The alarm flashlight is ideal for women, children and the elderly.
2. Equipped with the latest CREE-S3-LED technology with a life-span of up to 100,000 hours.
3. Body made of aviation aluminum alloy for maximal durability.
4. The surface adopts hard oxidation treatment for extended wear-resistance and corrosion-resistance.

using the alarm-flashlight:

1. Press the button located on the back end of the flashlight to control the LED light. The flashlight has 3 different modes: 100% light, 30% light, and flashing SOS-light.
2. Press the button repeatedly to switch through the different modes: 100% light - 30% light - flashing SOS-light - off. By pressing the button longer, the flashlight can be switched off at any time.
3. To activate the alarm: Quickly double press the button. The acoustic alarm and flashing light are activated instantly.
4. To charge the integrated battery, rotate the swivel [3] to uncover the charging port [6] and plug in the included USB-cable into the flashlight and a USB-charging port (computer or power adapter). While the battery is loading, the LED charging indicator [7] is red. When the LED charging indicator is blue, charging is completed. After removing the USB cable, please rotate the swivel back to cover the charging port, preventing water to enter the flashlight.

product specifications:

model no	300150
material	aviation aircraft alloy
LED	USA CREE XPG2-S3
size	Ø31 x 98mm
weight	99g
modes	100%, 30%, SOS-flashing
luminosity	100-300lm
lighting range	approx. 30m
alarm volume	approx. 120dB
battery	1x 16340 (rechargeable)
battery service life	strong light: 90min / weak light: 180min / alarm: 160min

Importiert durch / imported by / importé par / geïmporteerd door:

kh-security GmbH & Co.KG
 Heidering 17
 D-65321 Heidenrod
 GERMANY
 Tel. +49 (0)6124 72 79 80
 www.kh-security.de

