

Overview

1. Multifunction Button For Bluetooth® Pairing / Play / Pause
2. Mode Button Change from Bluetooth® Aux-in → MicroSD → USB Audio

AUX-IN (Blue)
SD CARD (Green)
USB AUDIO (Purple)

Vol - Vol +

100% - 75%
75% - 50%
50% - 25%
25% - 1%

PC/MAC

* (Not included)

Source Selection

Bluetooth®
USB Audio
SD Card

Source: Bluetooth®

LED: 5 Blue dots

M + - = ⏮
M + + = ⏭

Aux-in

Take call
Mute call
Reject call

Mobile Device
PC/MAC

Wireless Stereo: Link

LED: 5 Blue dots

Wireless Stereo: Unlink

LED: 5 Blue dots

AUX-IN
USB Audio
SD Card
Bluetooth®

Register your products at www.creative.com/register

TECHNICAL SUPPORT www.creative.com/support

© 2016 Creative Labs Pte. Ltd. All rights reserved. Creative, the Creative logo, and MUVO are trademarks or registered trademarks of Creative Technology Ltd in the United States and/or other countries. The Bluetooth® word mark and logo are owned by the Bluetooth® SIG, Inc. and any use of such marks by Creative Technology Ltd is under license. microSDHC, microSDXC logos are trademarks of SD-3C, LLC. All other trademarks are the property of their respective owners and are hereby recognized as such. All specifications are subject to change without notice. Actual product may differ slightly from images shown. Use of this product is subject to a limited warranty.

EN | Technical Specifications

Bluetooth® Version: Bluetooth® 4.2
Operating Frequency: 2402 - 2480 MHz
Operating Range: Up to 10 meters, measured in open space. Walls and structures may affect range of device.
Supported Bluetooth® Profiles: A2DP (Wireless Stereo Bluetooth®), AVRCP (Bluetooth® Remote Control), HFP (Handsfree profile)
Supported Codec: SBC
Supported Audio Formats (For SD card playback): MP3, WAV, WMA, FLAC
Does not support WMA PRO/lossless, (Extra High and above)
Support USB Audio for PC/MAC
Lithium Ion Battery: 3.7V 650mAh (2.41Wh)
Input: 5V 650mA
Battery Saving Mode: The speaker automatically powers down when there is no Bluetooth® connection or no audio cable attached for more than 10 minutes.
Operating Temperature Range: 0°C - 45°C
Note: Compliance markings are located on the bottom of this product.
*** Not Included. Sold Separately.**

Other Information

For the latest, online version of this guide, DoC and supplementary documentation such as safety and regulatory information for this product, please visit creative.com/support/muvo2c
Detailed instructions on removal of integrated battery can be found at Quickstart User Guide / Safety and Regulatory Information (creative.com/support/muvo2c), these instructions are meant strictly for independently qualified professionals.

Notice for Singapore
Complies with IDA Standards DA 107311

Source: SD Card

MicroSD (SD Card 128GB Max)
Fat 16, 32
MP3, WMA, Flac, WAV

M + - = ⏮
M + + = ⏭

Read SD Card

PC/MAC

Source: USB Audio

M + - = ⏮
M + + = ⏭

creative.com/support/muvo2c
日本語: jp.creative.com/downloads/muvo2c

