

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638120800](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 20-30 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)


**General**

Product Family	Application Tooling
Series	<a href="#">207121</a>
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Insertion Hand Tool
UPC	884982223400
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**  
[Application Tooling Documents](#)

ATS-638120800-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207121](#) Series

**Use With**

[43030](#) , [43031](#) , [44372](#) Micro-Fit 3.0 Male and Female Crimp Terminal, 20-30 AWG

**Application Tooling | FAQ**

Description	Product #
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 26-30 AWG	<a href="#">2064600011</a>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 26-30 AWG	<a href="#">2064600012</a>
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 26-30 AWG	<a href="#">2064600013</a>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 20-24 AWG	<a href="#">2064600021</a>
Micro-Fit+ Crimp Terminal, Female,	<a href="#">2064600022</a>

0.38µm Gold (Au)  
Plating, 20-24 AWG  
Micro-Fit+ Crimp 2064600023  
Terminal, Female,  
0.75µm Gold (Au)  
Plating, 20-24 AWG  
Micro-Fit+ Crimp 2064600031  
Terminal, Female,  
Tin (Sn) Plating, 18  
AWG  
Micro-Fit+ Crimp 2064600032  
Terminal, Female,  
0.38µm Gold (Au)  
Plating, 18 AWG  
Micro-Fit+ Crimp 2064600033  
Terminal, Female,  
0.75µm Gold (Au)  
Plating, 18 AWG  
Micro-Fit+ Crimp 2064600041  
Terminal, Female,  
Tin (Sn) Plating, 16  
AWG  
Micro-Fit+ Crimp 2064600042  
Terminal, Female,  
0.38µm Gold (Au)  
Plating, 16 AWG  
Micro-Fit+ Crimp 2064600043  
Terminal, Female,  
0.75µm Gold (Au)  
Plating, 16 AWG  
Micro-Fit 3.0 Crimp 430300001  
Terminal, Female,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430300002  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Reel  
Micro-Fit 3.0 Crimp 430300003  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Reel  
Micro-Fit 3.0 Crimp 430300004  
Terminal, Female,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430300005  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
26-30 AWG, Reel  
Micro-Fit 3.0 Crimp 430300006  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor

Bronze Contact,  
26-30 AWG, Reel  
Micro-Fit 3.0 Crimp 430300007  
Terminal, Female,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Bag  
Micro-Fit 3.0 Crimp 430300008  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Bag  
Micro-Fit 3.0 Crimp 430300009  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Bag  
Micro-Fit 3.0 Crimp 430300010  
Terminal, Female,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Bag  
Micro-Fit 3.0 Crimp 430300011  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
26-30 AWG, Bag  
Micro-Fit 3.0 Crimp 430300012  
Terminal, Female,  
with Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
26-30 AWG, Bag  
Micro-Fit 3.0 Crimp 430300038  
Terminal, Female,  
with Tin (Sn)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max  
Insulation Outside  
Diameter, Reel  
Micro-Fit 3.0 430300039  
Crimp Terminal,  
Female, with 0.38 $\mu$ m  
Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max  
Insulation Outside  
Diameter, Reel  
Micro-Fit 3.0 430300040  
Crimp Terminal,  
Female, with 0.76 $\mu$ m  
Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max

Insulation Outside  
Diameter, Reel  
Micro-Fit 3.0 Crimp 430310001  
Terminal, Male,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310002  
Terminal, Male,  
with 0.38µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310003  
Terminal, Male,  
with 0.76µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310004  
Terminal, Male,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310005  
Terminal, Male,  
with 0.38µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310006  
Terminal, Male,  
with 0.76µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel  
Micro-Fit 3.0 Crimp 430310007  
Terminal, Male,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Bag  
Micro-Fit 3.0 Crimp 430310008  
Terminal, Male,  
with 0.38µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Bag  
Micro-Fit 3.0 Crimp 430310009  
Terminal, Male,  
with 0.76µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Bag  
Micro-Fit 3.0 Crimp 430310010  
Terminal, Male,  
with Tin (Sn) Plated

Phosphor Bronze  
Contact, 26-30 AWG,  
Bag

Micro-Fit 3.0 Crimp 430310011  
Terminal, Male,  
with 0.38 $\mu$ m Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Bag

Micro-Fit 3.0 Crimp 430310012  
Terminal, Male,  
with 0.76 $\mu$ m Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Bag

Micro-Fit 3.0 Crimp 430310021  
Terminal, Male,  
with Tin (Sn)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max  
Insulation Outside  
Diameter, Reel

Micro-Fit 3.0 430310022  
Crimp Terminal,  
Male, with 0.38 $\mu$ m  
Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max  
Insulation Outside  
Diameter, Reel

Micro-Fit 3.0 430310023  
Crimp Terminal,  
Male, with 0.76 $\mu$ m  
Select Gold (Au)  
Plated Phosphor  
Bronze Contact,  
18 AWG, .073in /  
1.85mm Max  
Insulation Outside  
Diameter, Reel

Micro-Fit TPA Crimp 430315003  
Terminal, Male, with  
Tin (Sn) Pre-plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

Micro-Fit TPA Crimp 430315004  
Terminal, Male,  
with 0.38 $\mu$ m Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

Micro-Fit TPA Crimp 430315005  
Terminal, Male,  
with 0.76 $\mu$ m Select  
Gold (Au) Plated  
Phosphor Bronze

Contact, 20-24 AWG,  
Reel

Micro-Fit TPA Crimp [430315006](#)  
Terminal, Male, with  
2.54µm Matte Tin  
Plated Phosphor  
Bronze Contact,  
20-24 AWG, Reel

Micro-Fit TPA Crimp [430315007](#)  
Terminal, Male, with  
Tin (Sn) Pre-plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel

Micro-Fit TPA Crimp [430315008](#)  
Terminal, Male,  
with 0.38µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel

Micro-Fit TPA Crimp [430315009](#)  
Terminal, Male,  
with 0.76µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel

Micro-Fit TPA Crimp [430315010](#)  
Terminal, Male, with  
2.54µm Matte Tin  
Plated Phosphor  
Bronze Contact,  
26-30 AWG, Reel

Micro-Fit 3.0 Crimp [457730001](#)  
Terminal, Female,  
with Lubricant, with  
Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

Micro-Fit 3.0 Crimp [457730003](#)  
Terminal, Female,  
with Lubricant, with  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

Micro-Fit 3.0 Crimp [457730006](#)  
Terminal, Female,  
with Lubricant, with  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 26-30 AWG,  
Reel

Micro-Fit 3.0 Crimp [457730053](#)  
Terminal, Female,  
with Lubricant, with  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

CRC Signal Male [561168228](#)  
Terminal, Lead-Free,

Chain, Gold (Au)  
Plating  
CRC Signal Male [561168328](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating  
CRC Signal Male [561178228](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Male [561178328](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating  
CRC Signal Male [561188228](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Male [561188328](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating  
CRC Signal Male [561198228](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Female [561208428](#)  
Terminal, Lead-Free,  
Gold (Au) Plating,  
24-28 AWG, Reel  
CRC Signal Female [561208528](#)  
Terminal, Lead-Free,  
Gold (Au) Plating,  
24-28 AWG, Bag  
CRC Signal Female [561208628](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Female [561208728](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating  
CRC Signal Female [561218428](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Female [561218528](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating  
CRC Signal Female [561218628](#)  
Terminal, Lead-Free,  
Chain, Gold (Au)  
Plating  
CRC Signal Female [561218728](#)  
Terminal, Lead-Free,  
Loose, Gold (Au)  
Plating

This document was generated on 11/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**