

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192760002

Status:

Active

Overview:

Quixon Terminals

Description:

Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Red, 18-22 AWG, Loose



Documents:	
3D Model	Product Specification PS-19902-012-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-013-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)	

Agency Certification	
CSA	LR18689
UL	E79133
General	
Product Family	Quick Disconnects
Series	19276
Comments	Low Insertion Force
Crimp Quality Equipment	Yes
Insulated	Fully
Overview	Quixon Terminals
Product Name	InsulKrimp, Quixon
Type	Quick Disconnect
UPC	884982565081
Physical	
Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.920/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	3.43mm
Wire Size AWG	18, 20, 22
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	AA-2201-LIF
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-012-001, PS-19902-013-001
Sales Drawing	SD-19276-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19276 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
PremiumGrade	640010400
Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 10-22 AWG	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050400

This document was generated on 02/02/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION