

## Tuotekortti Product card



### **VA03-0033**

**JH-jatkoliitin 0,75**  
**JH-splice connector 0,75**

**Tuotetiedot**


Tuotekoodi	<b>VA03-0033</b>	Sähkönumero	<b>5206600</b>	EAN-koodi	<b>6410052066000</b>
Tuotenimi	JH-jatkoliitin 0,75	ETIM-luokka	<b>EC001059</b>		
Johtimet	Cu 0,75 mm <sup>2</sup>				

**Tekniset tiedot**

	-		
	-		
	-		
	-		
	-		
	-		
	-		
Napaluku	<b>1</b>	kpl	
	-		
	-		
	-		
	-		
	-		
	-		
	-		
Paino	<b>1</b>	g	
	-		
	-		
Väri / Materiaali	<b>Tinapinnoitettu kupari</b>		
Kiinnitys / Kytkeä	<b>Puristus</b>		

**Kuvaus**

Ounevan JH-jatkoliitintä käytetään kuparijohtimien ja käämien jatkamiseen. Liittimet on valmistettu 99,9 % puhtaasta kuparista ja pinnoitettu tinalla. Asennuksessa käytetään tavanomaisia puristustyökaluja.

**Mittakuva****Pakkaus**

Pakkausmuoto	<b>Pussi</b>	Kpl / Pakkaus	<b>100</b>	Paino [kg]	<b>0,05</b>
Pituus [mm]	<b>14</b>	Leveys [mm]	<b>60</b>	Korkeus [mm]	<b>110</b>

**Ouneva Oy**

Teollisuustie 21  
FI-82730 Tuupovaara  
Finland

Tel. +358 400 179 750  
[info@ouneva.fi](mailto:info@ouneva.fi)

[www.ounevagroup.fi](http://www.ounevagroup.fi)  
[www.ounevaproducts.fi](http://www.ounevaproducts.fi)

**Product data**


Product code	<b>VA03-0033</b>	STK-code	<b>5206600</b>	EAN-code	<b>6410052066000</b>
Product name	<b>JH-splice connector 0,75</b>			ETIM class	<b>EC001059</b>
Wires	<b>Cu 0,75 mm<sup>2</sup></b>				

**Technical data**

	-	
	-	
	-	
	-	
	-	
	-	
	-	
Number of poles	<b>1</b>	pcs
	-	
	-	
	-	
	-	
	-	
	-	
	-	
	-	
Weight	<b>1</b>	g
	-	
	-	
Color / Material	<b>Tin plated copper</b>	
Mounting / Connection	<b>Crimping</b>	

**Description**

JH Splice sleeves are designed for extending and branching of copper cables and coils. Installation of the sleeves can be performed with the most basic crimping tools.

**Drawing****Package**

Package	<b>Bag</b>	Pcs / Package	<b>100</b>	Weight [kg]	<b>0,05</b>
Length [mm]	<b>14</b>	Width [mm]	<b>60</b>	Height [mm]	<b>110</b>

**Ouneva Oy**

Teollisuustie 21  
FI-82730 Tuupovaara  
Finland

Tel. +358 400 179 750  
[info@ouneva.fi](mailto:info@ouneva.fi)

[www.ounevagroup.fi](http://www.ounevagroup.fi)  
[www.ounevaproducts.fi](http://www.ounevaproducts.fi)