

DATA SHEET

Creation Date: 12. Aug 2020 12:20
Page 1

MÜLLER LICHT

MÜLLER-LICHT International GmbH
Goebelstraße 61/63 – 28865 Liienthal – Tel./Phone: +49-4298-93700 – Fax: +49-4298-9370555

Our registered trademarks:

MÜLLER
LICHT

Starlicht

Technical details

Item-No. **404041**
Item Group: **LED/Outdoor-Wegeleuchten/Strom**
Description **tint LED Garden Lights Flores, 3 pcs, white+color**



Technology

Product data

Length [mm] **195**

Electrical data

Voltage nominal [V] **220-240**
Voltage measured [V] **230**
Power nominal [W] **13.00**
Power measured [W] **13.00**

Lighting data

Luminous flux nominal [lm] **540**
Luminous flux rated [lm] **540**
Luminous flux maximal [lm] **540**
Candela nominal [cd] **43**
Candela measured [cd] **43**

Environmental data

Information

Luminaire data

List of components
Cable ending
**3x Gartenspot IP65 mit Erdspieß
Netzteil (Primär 230-240 V/50 Hz, Sekundär
21 V DC), IP44
Anschlussleitung IP44, 9 m
Bedienungsanleitung**
CEE 7/17 unearthed plug

Driver

IP **44**
Owner name **Xing Yuan Electronics**

Packing

Colorbox

Weight [g] **170.00**
pcs. **1**

Blister

Inner box

Tray

Shrink

Transport carton

Weight [g] **280.00**
pcs. **2**

Manual

Notice

List of components
**3x tint Garden lights with Ground
spikes
Distribution wire
Plug-in power pack
Operating instructions**

Width [mm] **65**
Height [mm] **51**

Power max. [W] **7.08**
Lifetime nominal [h] **50000**
Frequency nominal [Hz] **50**
Power type **AC**
Current nominal [mA] **150**

Rated light efficiency nominal
[lm/W] **42**
Kelvin [K] **2700**
tint white+color
Light color **(1800-6500K+RGB)**
Color rendering index Ra [\geq] **80**

Cable sleeve **Rubber black**
Cable length [mm] **3000**
Protection class **III**

Type **XY-2100500-EO**
**main power plug adapter AC->AC/
DC(<=250W)**

Qty. of cont. products **3**
Barcode1 **4018412672872**
Code type 1 **EAN/UCC-13**

Weight [g] **0.00**

Weight [g] **0.00**

Weight [g] **0.00**

Weight [g] **0.00**

Barcode1 **4018412672940**
Code type 1 **EAN/UCC-13**
Barcode2 **0194018412672943300002**

Weight [g] **1290.00**
CE **yes**

Electric power factor [\geq] **0.38**
Switch cycles before failure **100000**
Weighted power consum. [kWh/1000h] **13**

Std. deviation of color matching
initial [SDCM] [$<$] **6**

CE **yes**
WEEE **yes**

Code type 2 **EAN128**

DATA SHEET

Creation Date: 12. Aug 2020 12:20
Page 2

MÜLLER LICHT

MÜLLER-LICHT International GmbH
Goebelstraße 61/63 – 28865 Lilienthal – Tel/Phone: +49-4298-93700 – Fax: +49-4298-9370555

Our registered trademarks:
MÜLLER
LICHT **Starlicht**

Technical details

Item-No. **404041**
Item Group: **LED/Outdoor-Wegeleuchten/Strom**
Description **tint LED Garden Lights Flores, 3 pcs, white+color**



Spectrum

