

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190080063

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Flag Krimptite Quick Disconnect, Female, for 10-12 (3.30 to 5.00mm²) Wire, Tab 6.35 x 0.81mm

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-19902-005-001 (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family

Series

Crimp Quality Equipment

Insulated

Overview

Product Name

Type

UPC

Quick Disconnects

19008

Yes

No

Standard Quick-Disconnect Terminals

Krimptite

Quick Disconnect

800755046786

Physical

Barrel Type

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Orientation

Packaging Type

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Closed

Female

No

None

None

Brass

Tin

Tin

0.970/g

Flag

Bag

No

0.81mm

6.35mm

Per Wire Specification

Crimp or Compression

10, 12

Electrical

Voltage - Maximum

Per Wire Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

C-1012

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-005-001, PS-19902-011-001, PS-19902-013-001

SD-19008-010-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

19008 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640031600
Krimptite Quick Disconnects	
Air Powered Tool	640071600
Head	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION