

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2018410030

Status:

Active

Overview:

MultiCat Power Connectors with Precision-Machined Contacts

Description:

MultiCat High-Power Inline Receptacle Housing, 3 Circuits, Black, Key A

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 2018400000-PS-000 (PDF)

Application Specification 2018400000-AS-000 (PDF)

Packaging Specification 2018410000-PK-000 (PDF)

Test Summary 2018400000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	201841
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
UPC	889056746403
Physical	
Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PEI
Net Weight	5.780/g
Number of Rows	1
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	7.40mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C
Material Info	
Engineering Number	2018410030-FCT
Reference - Drawing Numbers	
Application Specification	2018400000-AS-000
Packaging Specification	2018410000-PK-000
Product Specification	2018400000-PS-000
Sales Drawing	2018410000-SD-000
Test Summary	2018400000-TS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

201841 Series

Mates With

MultiCat High-Power Inline Plug Housing 201840 . MultiCat High-Power Header 201843 , 201842 . MultiCat Cable Assembly 451420301 , 451420310

Use With

MultiCat High-Power Contacts 201846 . MultiCat Female High-Power Pre-Crimped Lead 797582065 , 797582066 , 797582067 , 797582068 , 797582069 , 797582070

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION