



24P2QM

23 inch (60 cm) LCD MONITOR

23.8" VA FHD monitor with an eye for comfort, with height adjust stand and ergonomic features

General

Model name	24P2QM
EAN	4038986140713
Product Line	Pro-line
Series	P2
Channel	B2B
Classification	Mainstream
Section	Business
Launch date	2022-09-27T16:21:46+00:00
Continent	Europe
Product status (EU)	Launch

Screen

Resolution	1920x1080
Refresh rate	75Hz
Screen size (inch)	23 inch
Screen size (cm)	60 cm
Flat / Curved	Flat
Backlight	WLED
Panel Type	VA
Aspect ratio	16:9
Display Colours	16.7 Million
Panel Colour in Bits	8
sRGB Coverage (%) (CIE 1931)	127
Adobe RGB Coverage (%) (CIE 1931)	94
NTSC coverage (%) (CIE 1931)	90 %
Pixel Pitch	0.2745
Pixels per Inch	93
Response time (GtG)	4 ms
Contrast (static)	3000:1
Contrast (dynamic)	20M:1
Brightness (typical)	300 cd/m ²
Viewing angle (CR10)	178/178 °
OSD languages	EN, FR, ES, PT, DE, IT, NL, SE, FI, PL, CZ, RU, KR, CN (T), CN (S), JP

Exterior	
Monitor colour	Black
Bezel Type	3-sided frameless
Removable Stand	✓
Cable Management System	✓

Ergonomics	
Vesa Wallmount	100x100
Tilt	-5/23 °
Swivel	-180/180 °
Pivot	✓
Height Adjust Amount	150mm

Connectivity and Multimedia	
Signal Input	HDMI 1.4 x 1, DisplayPort 1.2 x 1, VGA, DVI
USB input	USB 3.2 (Gen1) x 4
USB Hub	✓
USB out ports	4
USB fast charge	✓

Multimedia	
Built-in Speakers	2 W x 2
Audio output	Headphone out (3,5mm)

Features	
Sync Technology	AdaptiveSync
Flicker-free	✓
Blue Light Technology	Low blue light

Sustainability	
HF	✓

Power / Environmental	
Powersupply	Internal
Powersource	100 - 240V 50/60Hz
Power Consumption On (Energystar test method)	20 watt
Power Consumption On	20
Power Consumption Standby	0.5 watt
Power Consumption Off	0.3 watt

Approbations / Regulations	
EPEAT	Yes
ISO 9241-307 class I	✓

Warranty	
Warranty Period	3 Years

Dimensions / Weights

Product Dimensions (incl base) (WxHxD) mm	540.2 x 384.4~513 x 200.1 inch
Product Dimensions (excl base) (WxHxD) mm	540.2 x 326.4 x 50.7 inch
Carton Dimensions (WxHxD) mm	812 x 590 x 322 mm
Product Dimensions (incl base) (WxHxD) mm	718.2 x 513.35 x 276.7 mm
Gross Weight (incl package) (kg)	7.24 Kg
Net Weight (excl package) (kg)	4.75 Kg

What's in the Box?

HDMI cable (m)	1,2 m
Micro HDMI to HDMI	✓