

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0522071860

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 18 Circuits, Gold Plating



Documents:	
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-52207-048-001 (PDF)	Reference Guide (PDF)
Packaging Specification SPK-52207-002-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52207
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	822350133968
Physical	
Actuator Type	Slider
Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	30
Flammability	94V-0
Mated Height	2.70mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	664.136/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-30° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52207 Series

Mates With

Premo-Flex FFC Cable [15039](#)

Reference - Drawing Numbers

Packaging Specification	SPK-52207-002-001
Product Specification	PS-52207-048-001
Sales Drawing	SD-52207-064-001, SD-52207-065-001, SD-52207-065-002, SD-52207-065-003, SD-52207-065-004, SD-52207-065-005

This document was generated on 12/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION