

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638199300

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for Cable Seal Crimp Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906603984
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-638199300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

MX150 Cable Seal Blade and Receptacle Crimp Terminals [34080](#) , [34081](#) , [34083](#)

Application Tooling Description	FAQ Product #
MX150 Cable Seal Male Terminal, Tin Plating, 22 AWG, Right Reel Payoff	340800003
MX150 Cable Seal Male Terminal, Gold Plating, 22 AWG, Right Reel Payoff	340800106
MX150 Cable Seal Male Terminal, Silver Plating, 22 AWG, Right Reel Payoff	340800206
MX150 Cable Seal Male Terminal, Tin Plating, 22 AWG, Left Reel Payoff	340801003

MX150 Cable Seal	340801106
Male Terminal, Gold	
Plating, 22 AWG,	
Left Reel Payoff	
MX150 Cable Seal	340801206
Male Terminal, Silver	
Plating, 22 AWG,	
Left Reel Payoff	
MX150 Cable Seal	340812005
Female Terminal,	
Gold Plating, 22	
AWG, Right Reel	
Payoff	
MX150 Cable Seal	340813005
Female Terminal,	
Gold Plating, 22	
AWG, Left Reel	
Payoff	
MX150 Cable Seal	340814003
Female Terminal,	
Silver Plating, 22	
AWG, Right Reel	
Payoff	
MX150 Cable Seal	340815003
Female Terminal,	
Silver Plating, 22	
AWG, Left Reel	
Payoff	
MX150 Cable Seal	340832003
Female Terminal,	
Tin Plating, 22 AWG,	
Right Reel Payoff	
MX150 Cable Seal	340833003
Female Terminal,	
Tin Plating, 22 AWG,	
Left Reel Payoff	