





PHILIPS

UltraEfficient Diamond Cut


Mounting Instructions



Model	Product Description	Power(W)	CRI(Ra)	CCT(K)	Total Lumen(lm)	Energy efficiency class of light source	Dimension AxB,C(mm)	Cut-Out D(mm)	Weight (kg)
9290041130	Diamond Cut UltraEfficient 80 30K	2	80	3000	310	B	φ95*49,5,48	φ68-80	0.08
9290041131	Diamond Cut UltraEfficient 80 40K	2	80	4000	310	B	φ95*49,5,48	φ68-80	0.08
9290041133	Diamond Cut UltraEfficient 90 30K	2.2	80	3000	345	B	φ105*49,5,48	φ80-90	0.096
9290041134	Diamond Cut UltraEfficient 90 40K	2.2	80	4000	345	B	φ105*49,5,48	φ80-90	0.096
9290041136	Diamond Cut UltraEfficient 125 30K	4.8	80	3000	800	B	φ145*49,5,48	φ120-130	0.152
9290041137	Diamond Cut UltraEfficient 125 40K	4.8	80	4000	800	B	φ145*49,5,48	φ120-130	0.152
9290041139	Diamond Cut UltraEfficient 150 30K	6.5	80	3000	1050	B	φ170*49,5,48	φ145-155	0.191
9290041140	Diamond Cut UltraEfficient 150 40K	6.5	80	4000	1050	B	φ170*49,5,48	φ145-155	0.191



Inrush Current



Model	9290041130 9290041131	9290041133 9290041134	9290041136 9290041137	9290041139 9290041140
Electrical characteristic				
I _{max} (A)	9.5	8.6	11.2	8.5
T _{ref} (μs)	0.13	0.13	0.15	0.1
MCB	Luminaires Max.(pcs)			
Type B-10A	68	76	40	76
Type B-16A	111	123	66	124
Type C-10A	116	128	69	129
Type C-16A	186	206	112	208



ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

- 01 Please read this manual before you start to install the luminaire.
- 02 The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations of the national requirements.
- 03 Switch OFF the power supply before the installation or maintenance to avoid electrical shock.
- 04 The luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc., are present.

ATTENTION: In B manual, you will find all the explanations with numeric reference to the icons respectively in front of these safety instructions.



3241 661 40241
© 2024 Signify Holding
Signify

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. and are used under license