



Einhell

EXPERT



Cordless Impact Drill

TE-CD 18/44 Li-i (1x2,5Ah)

Item No.: 4514287

Ident No.: 21014

Bar Code: 4006825679533

The cordless impact drill TE-CD 18/44 Li-i (1x2.5 Ah) is a member of the high-performance Power X-Change family. The 2-speed transmission is perfect for powerful drilling and screwing with up to 44 Nm of torque. The drill features speed electronics, 21 torque settings, a conventional drilling mode and a percussion drilling mode for working with harder materials such as brick or stone. The integrated LED illumination ensures a perfect view of the working area. The single-sleeve, 13 mm quick-action chuck is made of metal and allows tool accessories to be installed quickly. The tool comes with one 2.5 Ah Power X-Change battery and a charger.

Features & Benefits

- Member of the Power X-Change family, 1 x 18 V battery required
- Impact drilling function for drilling into stone and masonry
- 2-speed transmission for powerful drilling and screwing
- High-quality, 13 mm quick-release metal chuck
- Speed electronics to adapt to the material
- Ergonomic design with Softgrip inserts for comfortable operation
- Belt clip to attach the tool securely to the belt
- Integrated LED light to illuminate the work area
- Includes 1x 2.5 Ah Power X-Change battery and 1x charger



Technical Data

- Accumulator	18 V 2500 mAh Li-Ion
- Charging time	50min
- Number of gears	2
- Idle speed (gear 1)	0-400 min ⁻¹
- Idle speed (gear 2)	0-1500 min ⁻¹
- Max. torque hard	44 Nm
- Number of torque steps	21+1+1 settings
- Drill chuck	13 mm single sleeve
- Drilling capacity in concrete	10 mm
- Impact rate (gear 1)	0-6400 min ⁻¹
- Impact rate (gear 2)	0-24000 min ⁻¹
- Number of accumulators	1 Pieces



3 FUNCTIONS



ERGONOMIC




LED



INCL.

Logistic Data


- Product weight	1.59 kg
- Gross weight single packaging	2.73 kg
- Dimensions single packaging	170 x 233 x 231 mm
- Pieces per export carton	4 Pieces
- Gross weight export carton	10.92 kg
- Dimensions export carton	504 x 340 x 238 mm
- Container quantity (20"/40"/40"HC)	2740 5680 6640



18 V
2.5 Ah



44 Nm
HIGH POWER



3 FUNCTIONS

Available as special accessories



4-6 Ah Multi-Ah Power X-Change Plus Battery
Item No.: 4511502
Bar Code: 4006825644210



4,0 Ah Power X-Change Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



Power X-Fastcharger 4A Charger
Item No.: 4512103
Bar Code: 4006825650228
Einhell Accessory



Power X-Twincharger 3A Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



Power X-Car Charger 3A Charger
Item No.: 4512113
Bar Code: 4006825655377
Einhell Accessory



2x 18V 5,2Ah PXC-Twinpack Battery
Item No.: 4511526
Bar Code: 4006825656695
Einhell Accessory



PXC Battery Mounting Gadget
PXC-Battery Accessory
Item No.: 4514155
Bar Code: 4006825658774
Einhell Accessory

Power X-Caravan Charger 3A Charger
Item No.: 4512136
Bar Code: 4006825664010
Einhell Accessory



18V 4-6Ah & 6A Boostcharger PXC-Starter-Kit
Item No.: 4512143
Bar Code: 4006825667653
Einhell Accessory



Bit-Bohrerbox 22tlg. S-Box Akku-Bohrschrauber-Zubehör
Item No.: 49108806
Bar Code: 4009311088062
Einhell Accessory



Bit-Bohrerbox 39tlg. L-Box Akku-Bohrschrauber-Zubehör
Item No.: 49108911
Bar Code: 4009311089113
Einhell Accessory



Power X-Boostcharger 8A Charger
Item No.: 4512155
Bar Code: 4006825670554
Einhell Accessory



PXC Battery Protector
PXC-Battery Accessory
Item No.: 4140151
Bar Code: 4006825670844
Einhell Accessory



18V 3,0Ah SEALED PXC Plus A2 Battery
Item No.: 4511618
Bar Code: 4006825672794
Einhell Accessory



18V 2,5Ah PXC Starter Kit PXC-Starter-Kit
Item No.: 4512097
Bar Code: 4006825646962
Einhell Accessory



2x2 Power X-Quattrocharger 4A Charger
Item No.: 4512102
Bar Code: 4006825649536
Einhell Accessory



2x 5,2Ah & Twincharger Kit PXC-Starter-Kit
Item No.: 4512108
Bar Code: 4006825652376
Einhell Accessory



18V 3,0 Ah Power-X-Change 1 Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



2x 4,0Ah & Twincharger Kit 1 PXC-Starter-Kit
Item No.: 4512112
Bar Code: 4006825655766
Einhell Accessory



5,2Ah & 4A Fastcharger PXC-Starter-Kit
Item No.: 4512114
Bar Code: 4006825656787
Einhell Accessory



3,0 Ah Power X-Change Plus Battery
Item No.: 4511501
Bar Code: 4006825644197
Einhell Accessory



18V 5-8Ah Multi-Ah PXC Plus Battery
Item No.: 4511600
Bar Code: 4006825665055
Einhell Accessory



3er Set POWERBOX Kassetten Akku-Schlagbohrmaschinen-Zubeh
Item No.: 49109157
Bar Code: 4009311091574



Bitsatz 34 tlg. S-Box Akku-Bohrschrauber-Zubehör
Item No.: 49108801
Bar Code: 4009311088017
Einhell Accessory



Bit-Bohrerbox 39tlg. L-Box Akku-Bohrschrauber-Zubehör
Item No.: 49108956
Bar Code: 4009311089564
Einhell Accessory



5,2 Ah Power X-Change Plus Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



18V 4,0Ah Power-X-Change Plus Battery
Item No.: 4511553
Bar Code: 4006825660869
Einhell Accessory



18V 4,0Ah SEALED PXC Plus A1 Battery
Item No.: 4511627
Bar Code: 4006825673227
Einhell Accessory



18V 4Ah PXC Plus Twinpack
Battery
Item No.: 4511629
Bar Code: 4006825673685
Einhell Accessory



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V Battery Charger 3,0A - PXC
Charger
Item No.: 4514095
Bar Code: 4006825655292
Einhell Accessory



18V 4,0Ah PXC Starter Kit B1
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory



18V 3Ah PXC Plus Twinpack
Battery
Item No.: 4511631
Bar Code: 4006825673692
Einhell Accessory



2,0 Ah Power X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



5,2 Ah PXC Starter-Kit
PXC-Starter-Kit
Item No.: 4512147
Bar Code: 4006825675153
Einhell Accessory



2x18V 4,0Ah PXC-Twinpack CB
B1
Battery
Item No.: 4511489
Bar Code: 4006825638578

Battery-Running-Times

One Battery for All	
	screwing ¹ (pieces)
1.5 Ah	230
2.0 Ah	305
2.5 Ah	380
3.0 Ah	460
4.0 Ah	610
5.2 Ah	770
6.0 Ah	920
8.0 Ah	1220

Test setup:

1) wood - holes 6x45 mm