

LED 1000 BEDIENUNGSANLEITUNG

Artikelnr. 11 1585

Achtung: Lesen Sie vor dem Gebrauch des Produktes diese Gebrauchsanweisung bitte aufmerksam durch und bewahren Sie sie anschließend gut auf!

Lieferumfang: LED-Strahler, Ladekabel, Netzstecker, Bedienungsanleitung

Bedienung (Ein/Aus, Dimmen): Ein/Ausschalten: den Power-Knopf drücken.
Der LED-Strahler schaltet standardmäßig auf der höchsten Helligkeitsstufe ein.

Dimmen: 1 x kurzes Drücken des Ein-/Ausschalters.
Der Strahler verfügt über 2 Dimmstufen (1000 / 500 lm)

Hinweis: Der Strahler verfügt seitlich über eine Status-LED: rot = Akku nicht vollständig geladen, rot/grün blinkend = Ladevorgang läuft, grün = Strahler ist vollständig aufgeladen.

Sicherheitshinweise: Überprüfen Sie vor jeder Benutzung das Produkt auf etwaige Beschädigungen. Benutzen Sie das Produkt niemals, wenn Sie Beschädigungen feststellen. Wenden Sie sich in diesem Fall an eine Elektrofachkraft oder an die angegebene Serviceadresse des Herstellers. Öffnen Sie niemals das Akku-Gehäuse. Laden Sie den Strahler nicht im feuchten Zustand oder bei Temperaturen $<0^{\circ}\text{C}$ bzw. $>45^{\circ}\text{C}$. Ladegerät entfernen wenn Strahler ausreichend geladen. Die Lichtquelle sowie die Schutzabdeckung können nicht ersetzt werden. Schutzart IP65.

Wartung/Pflege: Der Strahler benötigt wenig Pflege und Wartung. Reinigen Sie das Glas und Gehäuse bei Bedarf mit einem nicht-scheuernden Mittel.

Stativmontage: Der Strahler kann auf ein handelsübliches Stativ aufgesetzt werden.



cimco

CIMCO Werkzeuge GmbH & Co. KG
Hohenhagener Straße 1 – 5, D-42855 Remscheid
www.cimco.de

LED 1000 USER MANUAL

Item no. 11 1585

Warning: Get to know your LED work light. Do not use until you have read and understood this instruction manual

Scope of delivery: LED work light, charging cable, plug, manual

Operation (On/Off, Dim): On/Off: press the power button.
The LED work light starts on the brightest light level as standard.

Dim: 1x short pressing of the On/Off button.
The work light provides 2 dim levels (1000 / 500 lm)

Note: The work light comes with an indicating LED: A solid red light indicates the battery is charging. A solid green light indicates charging is complete. Red/Green = charging in progress.

Safety instructions: Always check the product for damage before use. Never use the product in case of any damage. In case you find the product to be damaged, please refer to an electrician or the manufacturer's service address. Never attempt to open the battery for any reason. If battery housing has cracked, discontinue use immediately and do not try to recharge it. Never charge a wet LED work light or when work area or the temperature is below 0°C or above 45°C. Unplug charger when not in use. The light source and the protective cover cannot be replaced. Ingress protection IP65.



Maintenance/Service: Your work light requires very little care and maintenance.
Simply clean the lens regularly with a non-abrasive cleaner

Tripod installation: The work light can be mounted onto standard tripods.

Handle



Fixing screw for rotation angle and tripod mounting



cimco

CIMCO Werkzeuge GmbH & Co. KG
Hohenhagener Straße 1 – 5, D-42855 Remscheid
www.cimco.de