

One phone for every part of your day.

Because there's little difference between work, play and life, the Sonim XP400 is built to make a big difference.



sonim XP400



Tough and rugged, ohne Verzicht auf Performance.

Jeder Tag erfordert, dass Sie nahtlos zwischen Arbeit, Freizeit und Privatleben wechseln. Deshalb haben wir ein Smartphone entwickelt, das dies auch kann. Das Sonim XP400 kann alles bewältigen, was Sie von ihm verlangen, ohne dass Sie dafür Kompromisse eingehen müssen. Robuste Konstruktion, konstante Leistung und zahlreiche Funktionen machen es so robust wie Sie.

Unterstützt von Sonim

Seit 1999 ist Sonim der führende Anbieter robuster, zuverlässiger Mobilgeräte. In diesen 25 Jahren haben wir es uns zur Aufgabe gemacht, Menschen mit anspruchsvollen Aufgaben oder einem aktiven Leben Werkzeuge zu bieten, auf die sie sich verlassen können, um ihre Bedürfnisse zu erfüllen. Wir sind stolz auf das, was wir erreicht haben, freuen uns aber noch mehr auf das, was vor uns liegt. Weitere Informationen finden Sie unter www.sonimtech.com. Weitere Informationen finden Sie unter sonimtech.com

Features



Erfüllt den military standard (MIL-STD-810H, IP68) als Helfer gegen Schmutz, Staub und Wasser



Schnelle 5G und Wi-Fi connectivity
Hält dich **connected den ganzen Tag**



Großes 6.5" drop-resistant Bildschirm für optimale Helligkeit auch im Freien.




Push-to-Talk programmierbarer Knopf für einfache und effiziente Anwendung



Optimiert dein mobiles ecosystem und Produktivität mit dem bereits installierten SonimWare Software tool für Apps and Anwendungen

Sonim XP400

technische spezifikationen



Core Platform/Functions

Operating System	Android 14
Chipset	SM4450
Bands	5G: n1, n3, n5, n7, n8, n20, n26, n28, n38, n40, n41, n71, n75, n77, n78 LTE: 1, 3, 5, 7, 8, 20, 26, 28, 32, 38, 40, 41, 42, 68, 71 UMTS: I, II, IV, V, VIII GSM: 850/900/1800/1900MHz
Wi-Fi	802.11 a/b/g/n/ac, 2.4GHz/5GHz
Memory	6 GB RAM/128GB ROM Supports up to 2TB MicroSD external memory

Connectivity

Bluetooth	BT5.1
Messaging	SMS, MMS (Text, Image, Audio, Video)
GPS	GPS L1 & L5/A-GPS, GLONASS, Galileo
NFC	Yes
Sensors	Accelerometer, Ambient Light, Barometer, Gyroscope, Facial Recognition, Fingerprint, Magnetic Compass, Proximity
Language Supported	Global languages
VoLTE	Yes

Battery

Capacity	5000mAh
Battery Life	Talk: 30 hrs; Standby: 500 hrs

Display

Size/Type	6.5", Corning® Gorilla® Glass Victus II
Resolution	720x1612
Colors	16.7M

Physical Characteristics

Size	170 x 78 x 10.2 mm
Weight	230g
Ports	USB 3.1 Type-C
SIM Type	Dual 4FF SIM DSDS
Rugged Certifications	MIL-STD-810H; IP68
Operating Temperature	-20°C ~ +55°C

Audio

Microphone	Dual mic solution with noise cancellation
Speaker	Dual speaker
HAC	ANSI 2019

Multimedia

Audio Formats	AMR-NB, AMR-WB, AAC, AAC+, AAC+V2, MP3, V-SELP, AMR 12.65, AMR 6.6
Video Formats	3GP, MP4, AVI, MOV, MPEG-4, H.263, H.264, H.265
Graphic	BMP, GIF, JPEG, PNG, HEIF, WebP
Media Player	Yes
Camera	Dual rear 50MP standard and 5MP wide; 8MP front
LED Flashlight	Yes

Inbox Items

XP400, USB cable, SIM Tool, QSG