

BRUMBERG
Light. Since 1873.

PEPA Flache 48 V-Stromschiene, Länge: 3.000 mm

Article no. 88487380





IP20 48 V III

Tender
Flache 48 V-Stromschiene, Länge: 3.000 mm, black, Rectangular.Surface mounting, Ceiling-/Wall-/Pendant-mounted Mounting method: Surface mounting, Place of installation: Ceiling-/Wall-/Pendant-mounted, Material: Aluminium, Degree of protection: according to DIN EN 60529 IP20, Protection class: (EN 61140) III, Voltage: 48 V DC.


All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 27.06.2025 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flache 48 V-Stromschiene, Länge: 3.000 mm

Article no. 88487380

Leistung	maximale Schienenlänge in Metern
100 Watt	50 m
250 Watt	35 m
Angabe beziehen sich auf eine Last, die der gelieferten Leistung entspricht und gleichmäßig auf die entsprechende Länge in der Tabelle verteilt ist.	



Article data	
Article no.	88487380
GTIN	4255752520177
Series name	PEPA
Short description	Flache 48 V-Stromschiene, Länge: 3.000 mm
Material	Aluminium
Colour	Black
Type of surface	Structure
Shape	Rectangular
Length	3,000 mm
Width	26.2 mm
Hight	21 mm
Weight	2.1 kg
stamp	ENEC
Conformance	CE, UKCA

Operating technology of the luminaire	
Voltage type	DC
DC nominal voltage min	48 V
DC nominal voltage max	48 V
Protection class	III
Degree of protection	IP20
Wire number	4

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 27.06.2025 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flache 48 V-Stromschiene, Länge: 3.000 mm

Article no. 88487380

Operating technology of driver	
DC nominal voltage min	48 V
DC nominal voltage max	48 V
Protection class	III
Degree of protection	IP20
Nominal cross-section	2.00 mm2

Mounting technology	
Mounting method	Surface mounting
Place of installation	Ceiling-/Wall-/Pendant-mounted

Packing data	
Gross weight	2.12 kg
Length of packaging	3,002 mm
Packaging width	26 mm
Packaging hight	22 mm
Disposal at end of life	This product must not be disposed of with household waste. You are obliged, to dispose of such electrical waste separately. By disposing of electrical waste and other old or defective electronics separately, you support recycling or other forms of re-use. In that way you help to take care and to avoid that harmful substances get into the environment.

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 27.06.2025 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flache 48 V-Stromschiene, Länge: 3.000 mm

Article no. 88487380

Optional accessories
Article no.: 88482080 End piece for 48 V track DALI / without cable hole Dimensions: 26.4 mm x 21 mm x 2.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88482080_2021_DE.pdf
Article no.: 88482180 End piece for 48 V track DALI / with cable hole Dimensions: 26.4 mm x 21 mm x 2.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88482180_2021_DE.pdf
Article no.: 88484080 L-connector 90° to 48 V track Dimensions: 105 mm x 105 mm x 18.7 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484080_2021_DE.pdf
Article no.: 88484180 Flexible connector for 48 V track Dimensions: 273.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484180_2021_DE.pdf
Article no.: 88484280 Final power supply to 48 V track Dimensions: 111.7 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484280_2021_DE.pdf
Article no.: 88484380 Electrical connector for 48 V track Dimensions: 105 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484380_2021_DE.pdf
Article no.: 17480100 LED-Konverter zu 48 V-Schienensystem, DALI-Signal wird durchgeschliffen und muss sep. zugeführt werden Power: 1 - 100 W Dimensions: 298 mm x 16 mm x 19 mm https://www.brumberg.com/fileadmin/products/Datenblatt_17480100_2021_DE.pdf
Article no.: 17480200 LED-Konverter zu 48 V-Schienensystem, DALI-Signal wird durchgeschliffen und muss sep. zugeführt werden Power: 1 - 250 W Dimensions: 268 mm x 22 mm x 43.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_17480200_2021_DE.pdf
Article no.: 81107000 Stromschienen-Zange zu 3-Phasen-Stromschiene ONETRACK, DALI / schaltbar und 48 V Schienen (87161.. bis 87163.., bzw. 88487... bis 84888...)
Article no.: 88488700 Seilabhängung mit Schnellspanner zur flachen 48 V-Stromschiene Dimensions: 35 mm x 26.2 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488700_2021_DE.pdf

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 27.06.2025 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flache 48 V-Stromschiene, Länge: 3.000 mm
Article no. 88487380

Optional accessories
Article no.: 88488730 Seilabhängung mit Schnellspanner zur flachen 48 V-Stromschiene Dimensions: 35 mm x 26.2 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488730_2021_DE.pdf
Article no.: 88488750 Seilabhängung mit Schnellspanner zur flachen 48 V-Stromschiene Dimensions: 35 mm x 26.2 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488750_2021_DE.pdf

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 27.06.2025 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/