

TRENDNET®

Quick Installation Guide


5-Port Industrial Gigabit PoE+
Wall-Mounted Front Access Switch
TI-PG50F

8-Port Industrial Gigabit PoE+
Wall-Mounted Front Access Switch
TI-PG80F

1 Connect your switch to a power supply (TI-S24048 shown in picture not included)


2 Plug in your power supply to a power source.

3 Connect a port to your network (Optional)



Power Adapter

TI-PG50F




PoE Camera




4


PoE Access Point



Wall Mounting



DIN-Rail




Wall Mounting or Din-Rail are optional

LED	Color	Description
P1	Green	ON — Power 1 is detected
P2	Green	ON — Power 2 is detected
P3	Green	ON — Power 3 is detected for Power DIN
RLY	Amber	ON — Either PW1 or PW2 is disconnected OFF — Both PW1 and PW2 are connected
RJ-45 PORT		
LNK	Green	ON — TX port is detected Flashing — TX data is transmitting/receiving
PoE	Amber	ON — PD is detected and PSE is activated OFF — PD is not detected

1 Connect your switch to a power supply (TI-S24048 shown in picture not included)


2 Plug in your power supply to a power source.

3 Connect a port to your network (Optional)




Power Adapter

TI-PG80F




PoE Camera




4


PoE Access Point



Wall Mounting



DIN-Rail



Wall Mounting or Din-Rail are optional

LED	Color	Description
P1	Green	ON — Power 1 is detected
P2	Green	ON — Power 2 is detected
P3	Green	ON — Power 3 is detected for Power DIN
RLY	Amber	ON — Either PW1 or PW2 is disconnected OFF — Both PW1 and PW2 are connected
RJ-45 PORT		
LNK	Green	ON — TX port is detected Flashing — TX data is transmitting/receiving
PoE	Amber	ON — PD is detected and PSE is activated OFF — PD is not detected

Declaration of Conformity

TRENDNET®

Manufacturer's Name and Address

TRENDnet, Inc.
20675 Manhattan Place
Torrance, CA 90501 USA

Zwolsestraat 156 2587 WB
The Hague The Netherlands



Product Information:

Model Number: TI-PG50F / TI-PG80F
Product Name: 5-Port Industrial Gigabit PoE+ Wall-Mounted Front Access Switch
8-Port Industrial Gigabit PoE+ Wall-Mounted Front Access Switch
Trade Name: TRENDnet

TRENDnet hereby declares that the product is in compliance with the essential requirements and other relevant provisions under our sole responsibility.

This product is herewith confirmed to comply with the Directives.

Measurement Standards: EN 55024:2010
EN 55032:2012/AC:2013
FCC Part 15B Class A

Directives: Low Voltage Directive 2014/35/EU
EMC Directive 2014/30/EU
RoHS Directive 2011/65/EU
REACH Regulation (EC) No. 1907/2006

Person responsible for this declaration.

Place of Issue: Torrance, California, USA

Date: February 05, 2019

Title: Director of Technology

Name: Sonny Su

Signature:



Déclaration de conformité

TRENDNET®

Nom et adresse du fabricant

TRENDnet, Inc.
20675 Manhattan Place
Torrance, CA 90501 USA

Zwolsestraat 156 2587 WB
The Hague The Netherlands



Détails du produit

Modèle: TI-PG50F / TI-PG80F
Nom du produit: Switch Industriel d'accès frontal et mural Gigabit PoE+ de 5 ports
Switch Industriel d'accès frontal et mural Gigabit PoE+ de 8 ports

Nom Commercial: TRENDnet

TRENDnet déclare par la présente que le produit est conforme aux exigences essentielles et aux autres dispositions pertinentes de la Directive en vertu de notre seule responsabilité.

Ce produit est conforme à la directives suivante.

Les standards de mesure: EN 55024:2010
EN 55032:2012/AC:2013
FCC Part 15B Class A

Directives: Directive Basse Tension 2014/35/UE
Directive CEM 2014/30/UE
Directive RoHS (UE) 2011/65/UE
REACH Règlement (CE) N° 1907/2006

Personne responsable de cette déclaration.

Lieu de délivrance: Torrance, California, USA

Date: 05 Février, 2019

Position: Director of Technology

Nom: Sonny Su

Signature:



Certifications

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference.
- (2) This device must accept any interference received. Including interference that may cause undesired operation.



Waste electrical and electronic products must not be disposed of with household waste. Please recycle where facilities exist. Check with your Local Authority or Retailer for recycling advice.

Applies to PoE Products Only: This product is to be connected only to PoE networks without routing to the outside plant.

Note

The Manufacturer is not responsible for any radio or TV interference caused by unauthorized modifications to this equipment. Such modifications could void the user's authority to operate the equipment.

Advertencia

En todos nuestros equipos se mencionan claramente las características del adaptador de alimentación necesario para su funcionamiento. El uso de un adaptador distinto al mencionado puede producir daños físicos y/o daños al equipo conectado. El adaptador de alimentación debe operar con voltaje y frecuencia de la energía eléctrica domiciliar existente en el país o zona de instalación.

Technical Support

If you have any questions regarding the product installation, please contact our Technical Support.

Toll free US/Canada: **1-866-845-3673**

Regional phone numbers available at www.trendnet.com/support

TRENDnet

20675 Manhattan Place
Torrance, CA 90501
USA

Limited Warranty

TRENDnet warrants its products against defects in material and workmanship, under normal use and service. Specific warranty periods are listed on each of the respective product pages on the TRENDnet website.

Garantie Limitée

TRENDnet garantit ses produits contre les problèmes de matériel ou de fabrication, dans des conditions normales d'utilisation et de service. Les périodes de garanties précises sont mentionnées sur chacun des pages produits du site web de TRENDnet.

Eingeschränkte Garantie

TRENDnet gewährt eine Garantie für seine Produkte im Falle von Material- und Bearbeitungsdefekten, bei normaler Verwendung und Wartung. Spezielle Garantiezeiträume werden auf jeder Produktseite auf der Website von TRENDnet genannt.

Garantía limitada

TRENDnet garantiza que sus productos carecen de defectos en el material y la fabricación, en condiciones de uso y funcionamiento normales. Los periodos específicos de garantía figuran en cada una de las páginas de producto del sitio web de TRENDnet.

Ограниченная гарантия

Компания TRENDnet предоставляет гарантию на свои изделия от дефектов материалов и сборки при нормальном использовании и обслуживании. Конкретные гарантийные сроки указаны на странице каждого продукта на сайте компании TRENDnet.

Garantia Limitada

A TRENDnet garante seus produtos contra defeitos de material e mão de obra sob condições normais de uso e serviço. Os períodos de garantia específicos estão listados em cada uma das páginas dos respectivos produtos no site da TRENDnet.

Piiratud garantii

TRENDneti garantii hõlmab materjali- ja koostamisdefekte, mis ilmnevad toote tavapärasel kasutamisel. Garantiaaja täpne pikkus konkreetselt toote puhul on leitav TRENDneti kodulehel vastava toote infolehel.

Garanzia limitata

TRENDnet garantisce i propri prodotti da difetti di materiali e manodopera, in condizioni di normale uso ed esercizio. I periodi di garanzia specifici sono elencati sulle rispettive pagine di prodotto sul sito TRENDnet.