

Product information

00 21 50 S

Tool backpack Modular X18 Plumbing

17 parts



- Fits you and your tools: practical and comfortable due to fully hinged front and back, removable tool board and padding for your back
- As individual as you are: Optimal flexibility due to innovative FIDLOCK® connectors and MOLLE webbing
- Fit for any challenge: with two separate inner compartments for tools, measuring instruments, notebook or tablet
- Equipped with 12 KNIPEX tools, a total of 17 brand tools, partly VDE-tested according to DIN EN 60900
- Durable fabric made of sustainable recycled synthetic fibers, splash-proof and easy to clean
- Waterproof molded bottom made of impact-resistant plastic for a secure upright position when opened and closed, 6 cm high
- One MOLLE strap on the inside and four MOLLE straps on the outside for attaching any adapters, carabiners and accessories
- FIDLOCK® connections are fastened or unfastened in no time at all
- A total of 21 retaining loops and 37 pockets, some with zips
- Luggage strap for fixing to telescopic handles of tool cases
- 53 x 34 x 21 cm (H x W x D), empty weight 2.9 kg, tested load capacity up to 15 kg
- Max. payload: 15 kg
- Volume: 18 litres

General

Article No.	00 21 50 S
EAN	4003773089070
Weight	6,550 g
Dimensions	530 x 217 x 549 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	340 mm
Dimension exterior (interior) height mm	210 mm
Dimension exterior (interior) depth mm	530 mm

Content

86 03 300	1 x Pliers Wrench pliers and a wrench in a single tool (300 mm) 
87 01 300	1 x KNIPEX Cobra® High-Tech Water Pump Pliers (300 mm) 
90 22 10 BK	1 x KNIPEX BiX® Cutter for plastic pipes and sealing sleeves (72 mm)
90 31 02 SB	1 x KNIPEX TubiX® Pipe cutter (180 mm)
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm) ⚡ 1000V 
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (1,0 x 5,5 x 125 mm) ⚡ 1000V 
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1 x 80 mm) ⚡ 1000V 

Content	
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2 x 100 mm) ⚠ 1000V ⚡
00 11 01	1 x Knipex KNIPEX TwinKey® for all standard cabinets and shut-off systems (92 mm)
74 06 180	1 x Knipex High Leverage Diagonal Cutter (180 mm) ⚠ 1000V ⚡
87 01 180	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (180 mm) 🔧
01114	1 x Stabila Wooden folding rule type 1607, white (2.000 mm)
101-0300	1 x Picard Locksmith's hammer (300 g)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm) 🔩

Accessories	
00 21 50 LE	KNIPEX Modular X18 empty,

technical change and errors excepted

