



Einhell

CLASSIC



Cordless Angle Grinder

TC-AG 18/115 Li (1x4,0Ah)

Item No.: 4431133

Ident No.: 21014

Bar Code: 4006825679526

The Einhell wireless angle grinder TC-AG 18/115 Li (1x4.0Ah) is a light and therefore handy angle grinder with a cutting depth of maximum 28 mm and a disc diameter of 115 mm. Whether powerful cutting, grinding or polishing, with an idle speed of 8,500 rpm, the angle grinder is always a useful helper. Soft start and restart protection always ensure increased application safety, while overload protection in turn ensures the durability. Equipped with an ergonomic soft grip, the additional handle is flexible and can be assembled and fixed in 3 positions. Delivery includes 1x 4.0 Ah battery and a charging device. Supplied without cutting disc

Features & Benefits

- Part of the Power X-Change family, 1 x 18 V battery required
- Soft-start & protection against accidental restarts enhance user safety
- Overload protection protects the motor against overheating
- Additional handle can be mounted in 3 positions as required
- Support surface with elevations for secure storage
- Recommendation for optimal results: 2.5 Ah battery and above
- Supplied with 1x 4.0 Ah batteries and a charging device.
- Supplied without cutting disc




Technical Data

- | | |
|-------------------------------------|--------------------------|
| - Accumulator | 18 V 4000 mAh Li-Ion |
| - Charging time | 80min |
| - Mains supply charger | 200-250 V 50-60 Hz |
| - Disc size | 115 mm |
| - No-load speed (idle speed) Max. | 8500 min ⁻¹ |
| - Max. cutting depth | 28 mm |
| - Number of accumulators | 1 Pieces |

Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Product weight (kg) | 2.25 |
| - Gross weight (kg) | 3.61 |
| - Dimensions single packaging | 311 x 155 x 205 mm |
| - Pieces per export carton | 4 Pieces |
| - Gross weight of export carton | 15 kg |
| - Dimensions Export Carton | 630 x 328 x 220 mm |
| - Container quantity (20"/40"/40"HC) | 2520 5320 6384 |



Available as special accessories



4-6 Ah Multi-Ah Power X-Change Plus Battery
Item No.: 4511502
Bar Code: 4006825644210



4,0 Ah Power X-Change Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



Power X-Fastcharger 4A Charger
Item No.: 4512103
Bar Code: 4006825650228
Einhell Accessory



Power X-Twincharger 3A Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



Power X-Car Charger 3A Charger
Item No.: 4512113
Bar Code: 4006825655377
Einhell Accessory



2x 18V 5,2Ah PXC-Twinpack Battery
Item No.: 4511526
Bar Code: 4006825656695
Einhell Accessory



PXC Battery Mounting Gadget
PXC-Battery Accessory
Item No.: 4514155
Bar Code: 4006825658774
Einhell Accessory



DIA-Trennschleifer dünn 115x1,4 Winkelschleifer-Zubehör
Item No.: 49721150
Bar Code: 4009317211501
Einhell Accessory



10 Trennschei. dünn 115x1,0 Winkelschleifer-Zubehör
Item No.: 49711944
Bar Code: 4009317119449
Einhell Accessory



18V 5-8Ah Multi-Ah PXC Plus Battery
Item No.: 4511600
Bar Code: 4006825665055
Einhell Accessory



M14 Schnellspannmutter Winkelschleifer-Zubehör
Item No.: 49717705
Bar Code: 4009317177050
Einhell Accessory



5,2 Ah Power X-Change Plus Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



18V 4,0Ah Power-X-Change Plus Battery
Item No.: 4511553
Bar Code: 4006825660869
Einhell Accessory



18V 4,0Ah SEALED PXC Plus A1 Battery
Item No.: 4511627
Bar Code: 4006825673227
Einhell Accessory



18V 2,5Ah PXC Starter Kit PXC-Starter-Kit
Item No.: 4512097
Bar Code: 4006825646962
Einhell Accessory



2x2 Power X-Quattrocharger 4A Charger
Item No.: 4512102
Bar Code: 4006825649536
Einhell Accessory



2x 5,2Ah & Twincharger Kit PXC-Starter-Kit
Item No.: 4512108
Bar Code: 4006825652376
Einhell Accessory



18V 3,0 Ah Power-X-Change 1 Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



2x 4,0Ah & Twincharger Kit 1 PXC-Starter-Kit
Item No.: 4512112
Bar Code: 4006825655766
Einhell Accessory



5,2Ah & 4A Fastcharger PXC-Starter-Kit
Item No.: 4512114
Bar Code: 4006825656787
Einhell Accessory



3,0 Ah Power X-Change Plus Battery
Item No.: 4511501
Bar Code: 4006825644197
Einhell Accessory



Power X-Caravan Charger 3A Charger
Item No.: 4512136
Bar Code: 4006825664010
Einhell Accessory

2 Schleifmop 115 K 40/80 Winkelschleifer-Zubehör
Item No.: 49795505
Bar Code: 4009317955054
Einhell Accessory



18V 4-6Ah & 6A Boostcharger PXC-Starter-Kit
Item No.: 4512143
Bar Code: 4006825667653
Einhell Accessory



Power X-Boostcharger 8A Charger
Item No.: 4512155
Bar Code: 4006825670554
Einhell Accessory



PXC Battery Protector PXC-Battery Accessory
Item No.: 4140151
Bar Code: 4006825670844
Einhell Accessory



18V 3,0Ah SEALED PXC Plus A2 Battery
Item No.: 4511618
Bar Code: 4006825672794
Einhell Accessory



18V 4Ah PXC Plus Twinpack Battery
Item No.: 4511629
Bar Code: 4006825673685
Einhell Accessory



18V 3Ah PXC Plus Twinpack
Battery
Item No.: 4511631
Bar Code: 4006825673692
Einhell Accessory



2,0 Ah Power X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



5,2 Ah PXC Starter-Kit
PXC-Starter-Kit
Item No.: 4512147
Bar Code: 4006825675153
Einhell Accessory



2x18V 4,0Ah PXC-Twinpack CB
B1
Battery
Item No.: 4511489
Bar Code: 4006825638578



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V Battery Charger 3,0A - PXC
Charger
Item No.: 4514095
Bar Code: 4006825655292
Einhell Accessory



18V 4,0Ah PXC Starter Kit B1
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory

Battery-Running-Times

One Battery for All	
	cutting ¹ (pieces)
1.5 Ah	15
2.0 Ah	20
2.5 Ah	25
3.0 Ah	30
4.0 Ah	40
5.2 Ah	60
6.0 Ah	70
8.0 Ah	80

For best performance select a battery with at least 2.5 Ah

Test setup:

1) metal - round steel Ø 12 mm - Max. electronic speed