




LOC	DIST	REVISIONS					
CE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			I	NEW PRODUCT RELEASE	05MAY2006	BB	LS
			A	RELEASED PER ECR-07-004102	16MAR2007	JWD	LS

- 1 MATERIAL
CONNECTOR ASSEMBLY:
REAR BODY: NICKEL PLATED BRASS
FERRULE: STAINLESS STEEL
COUPLING NUT: NICKEL PLATED BRASS
PROTECTIVE CAP: VINYL, COLOR: RED
CRIMP EYELET: NICKEL PLATED BRASS
STRAIN RELIEF: POLYOLEFIN ELASTOMER, COLOR: BLACK*
*UL94 V-0 RATED AT QUALIFYING THICKNESS.
- 2 BULK PACKAGE.
3. COUPLING NUT NORMAL TIGHTENING TORQUE RANGE
IS 7.0 TO 10.0 in-lbf. DO NOT EXCEED 20 in-lbf.

2	BOOT NOT INCLUDED	140um	4-5504567-1
	STANDARD KIT	720um	3-5504567-9
	STANDARD KIT	.082in	3-5504567-3
	STANDARD KIT	.042in	2-5504567-9
	STANDARD KIT	140um	5504567-2
	STANDARD KIT	125um	5504567-1
	DESCRIPTION	FIBER HOLE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. BRIGGS 05MAY2006	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK L. SAUERWEIN 05MAY2006		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BUCHTER 05MAY2006	NAME CONNECTOR KIT, SMA 905 STAINLESS STEEL FRONT BODY, BRASS REAR BODY, 4.3mm CABLE	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
MATERIAL 1 -		CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779
			DRAWING NO 5504567	RESTRICTED TO -
			SCALE 4:1	SHEET 1
			OF 1	REV A