



microSD Cards
microSDXC/SDHC 500S

Transcend's microSDXC/SDHC 500S memory cards provide the performance and capacity necessary to harness the full power of your UHS-I compliant action camera and drone camera. In addition to incredible transfer speeds, the cards meet UHS Video Speed Class 30 (V30) standards, allowing for smooth, uninterrupted 4K video capture.

V30 standard compliance applies only to 16GB-64GB capacities.



Actions in detail

Transcend's microSDXC/SDHC 500S memory cards are manufactured with top-tier MLC NAND flash, making them durable and reliable. The cards offer impressive transfer rates and stable video recording without dropping frames, making them ideal for action cameras and drone cameras.



Show the transfer capabilities


Transcend's microSDXC/SDHC 500S memory cards meet both the UHS Speed Class 3 (U3) and the UHS Video Speed Class 30 (V30) standards for 4K Ultra HD video recordings, with read/write speeds of up to 95MB/s and 80MB/s respectively.

U3 and V30 compliance applies only to 16GB-64GB capacity cards.



Store as many as you wish

With up to 64GB storage capacity, Transcend's microSDXC/SDHC 500S memory cards allow for thousands of photos and hours of Full HD videos to be recorded, meaning you can stay focused on capturing fantastic moments without worrying about running out of storage.



microSD Cards microSDXC/SDHC 500S

Features

- Compliant with UHS Speed Class 3 (U3) and UHS Video Speed Class 30 (V30) standards
- Up to 95 MB/s read; 80 MB/s write
- MLC NAND flash memory
- Ideal for action cameras and drone cameras



RecoveRx

RecoveRx is a data recovery software for memory cards, USB flash drives, external hard drives and SSDs.

Specifications

Appearance

Dimensions	11 mm x 15 mm x 1 mm (0.43" x 0.59" x 0.04")
Weight	0.4 g (0.01 oz)

Storage

Capacity	8 GB / 16 GB / 32 GB / 64 GB
Flash Type	MLC NAND flash

Operating Environment

Operating Temperature	-25°C (-13°F) ~ 85°C (185°F)
-----------------------	------------------------------

Performance

Speed Class	UHS-I U3 UHS-I U1 Class 10 V30
Read Speed (Max.)	up to 95 MB/s
Write Speed (Max.)	up to 80 MB/s
Insertion/Removal Cycles	10,000
Note	Speed may vary due to host hardware, software, usage, and storage capacity.

Warranty

Certificate	CE / FCC / RCM / EAC
Warranty	Five-year Limited Warranty

Ordering Information

8GB	TS8GUSD500S
16GB	TS16GUSD500S
32GB	TS32GUSD500S
64GB	TS64GUSD500S

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.