



LOKLiK iCraft™



About LOKLiK

LOKLiK is an innovative DIY brand dedicated to catering to the needs of every craft lover with utmost dedication. As a trusted ally that truly understands crafters, LOKLiK strives to unlock the boundless realm of creativity.

Combining development, production, and sales, LOKLiK places significant emphasis on R&D investment and continuous innovation. It remains steadfast in upholding the founder's core mission: to deliver cutting-edge, user-friendly products that enhance efficiency and ignite creativity and eventually, be the global all-in-one DIY services platform.

LOKLiK iCraft™

iCraft My Way

Farewell to the tedious cutting process either by hand or a slow machine. The all-new LOKLiK iCraft™, tested for efficiency and precision cutting down to 0.5 mm, is your go-to craft companion. Equipped with a space-saving body and upgraded step motor, LOKLiK iCraft™ leads the way in masterful projects out of 100+ materials. Fine details and extensive design length are a breeze, as well. With the strong support of its connected software, LOKLiK IdeaStudio™, and art library, LOKLiK Workshop™, you're allowed to get inspired by over 18,000 free artistic and AI-generated images, even without design experience. Enjoy the journey of growing into a creative crafter with LOKLiK iCraft™!



FEATURES




Easy-cut All Your Daily Materials

100+ applicable DIY materials supported by the built-in step motor and high-quality blades walk you through more creative ideas, from unique cake ornaments and tutorial crafts to home and festive decor.



Perfect Stickers for Cuties

Blows the mind with complicated artwork of a print-then-cut precision down to 0.5 mm while making full use of the pre-installed photoelectric sensors and specific algorithms.




Larger Artwork at Your Fingertips

Even with a compact body of 51.5 cm in width, this machine can still take your hands-on ability to the next level with large matless projects of materials up to 6.4 m/21 ft in length.



AI-
Painting



Bust Out Your LOKLiK AI Crafts

LOKLiK IdeaStudio™ always serves as a fantastic addition to your crafting arsenal! With its highly matching cutter, you can craft beautifully AI-drawn designs into reality.



Boost Inspiration via Free Designs

Tap into our extensive collection of premade images, LOKLiK Workshop™. Over 18,000 free designs and 30 more fonts are there to streamline your crafting experience.


QUICK START



1



2



3



4

1. Power on your LOKLiK iCraft™;
2. Connect the machine to the LOKLiK IdeaStudio™ (or App: LOKLiK™);
3. Load the material and cutting mat into the machine;
4. Design your image and set up the cutting parameters to cut.

SPECIFICATIONS

Colors



Daisy White



Bubble Blue



Pastel Pink

Colors: Daisy White, Bubble Blue, Pastel Pink

Max Material Width: 30.5 cm/12 in (With Mat); 33 cm/13 in (Matless)

Max Cut Length: 61 cm/24 in (With Mat); 6.4 m/21 ft (Matless)

Compatible Materials: Heat Transfer Vinyl, Permanent Vinyl, Printable Vinyl, Board, Smart Vinyl, Cardstock, Plastic Board, Leather, Felt, Foam Board, etc.

Available Tools: Fine-point Blade, Deep-point Blade, Pen, Foil Transfer Tip, Scoring Stylus.

Max Material Height: 2 mm

Precision: 0.01 mm

Maximum Cutting Force: 5200gf of torque

Connectivity: USB, Bluetooth

Design Software: (Desktop) LOKLiK IdeaStudio™; (Mobile) LOKLiK™

Supported Systems: Windows 10 or later, Mac OS 11 or later

Dimensions: 51.5 x 14.0 x 14.5 cm / 20.3 x 5.5 x 5.7 in

Weight: 5.0 kg/11.0 lb

Input Power: 100-240V~ 50/60Hz 36W

