
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - ;- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST
GP	00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



1. PARTS PACKAGED UNASSEMBLED AS A UNIT KIT.
2. CABLE CLAMPS: ABS COMPOUND, COLOR BLACK.
   FILISTER HEAD SCREWS, HEX NUTS & MOUNTING SCREWS: STEEL.
   GROMMETS: FLEXIBLE PVC, UL 94V-0 RATED, COLOR BLACK.
3. CABLE CLAMPS: UNPLATED.
   FILISTER HEAD SCREWS, HEX NUTS & MOUNTING SCREWS: ZINC PLATED CLEAR CHROMATE COATED.
4. SIZE 3 CONFIGURATION SHOWN. NUMBER AND SIZE OF SLOTS IN THIS AREA VARIES BY CABLE CLAMP SIZE.



GROMMET ASSORTMENT
TYPE 1
SEE TABLE



GROMMET ASSORTMENT
TYPE 2
SEE TABLE

TYPE 2	.900	.730	2.644	1.920	2.406	5	5748678-5
TYPE 2	.800	.620	2.738	1.920	2.500	4	5748678-4
TYPE 2	.680	.640	2.090	1.920	1.852	3	5748678-3
TYPE 1	.620	.620	1.545	1.910	1.312	2	5748678-2
TYPE 1	.570	.630	1.215	1.910	.984	1	5748678-1
GROMMET ASSORTMENT	E	D	C	B	A	SIZE	PART NO

COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .005
4 PLC ± –
ANGLES ± –

MATERIAL 2
FINISH 3

DWN R.RICHARDSON 15SEP05
CHK C.ROHDE 15SEP05
APVD M.WALMSLEY 15SEP05
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –

TE Connectivity

NAME
KIT, CABLE CLAMP,
180 DEGREES EXIT, UNPLATED, BLACK,
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-5748678	–

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV A1

4805 (3/11)