

AccuLux FL 10000 W



Mobiler Arbeitsstrahler
mit 100 W LED für den In-
und Outdoorbereich.



Mobile work flood light
with 100 W LED for indoor
and outdoor use.

Merkmale:

- Aufladbarer robuster Arbeitsstrahler
- Extrem stoßfestes Kunststoffgehäuse
- Superhelle und breite Ausleuchtung
3 Lichtstufen: ca. 10.000 / 5.000 / 2.500
Lumen und SOS-Blinkfunktion
- Kann mit Kabel oder Akku betrieben werden
- Leuchtdauer im Akku-Betrieb: ca. 3 / 6 / 11h
bei 18V / 4,0 Ah Lithium-Ionen-Akku
(nicht im Lieferumfang enthalten)
- Anschluß f. Akkutyp Makita ohne Adapter möglich
- Adapter für Typen Bosch und Milwaukee
im Lieferumfang enthalten
- Akku-Ladezustandsanzeige
- Flexibel einstellbarer Leuchtwinkel
- Schutzart IPX4 (spritzwassergeschützt)
- 2 extrem starke Haftmagnete
- Gewicht (ohne Akku): 1,4kg
- 230V-Ladekabel 1,6m
- Maße: 263x198x135mm
- USB-Output: Leuchte als Powerbank nutzbar
- Lieferumfang: Leuchte + Ladekabel
+ 2 Akkuadapter (für Typen Bosch und Milwaukee)
- **Art. Nr. 447491**
- Akku-Typ Makita 18V / 4,0 Ah (kein Adapter nötig)
als Zubehör bestellbar (Art. Nr. 447810)

Features:

- Rechargeable robust work flood light
- Extremely impact-resistant plastic housing
- Extremely bright and wide illumination
3 light steps: ca. 10.000 / 5.000 / 2.500 lumens
and SOS flash function
- Can be operated with cable or battery
- Operating time on battery power:
ca. 3 / 6 / 11h with 18V / 4,0 Ah battery
(not included)
- Connection for battery type Makita possible
without adapter
- Adapter for types Bosch- and Milwaukee battery
Included
- Battery level indicator
- Flexible adjustable light angle
- Protection class: IPX4 (splash proof)
- 2 extremely strong magnets
- Weight (without battery): 1,4kg
- 230V charging cable 1,6m
- Dimensions: 263x198x135mm
- USB-output: can be used as a power bank
- Supply: flood light + charging cable
+ 2 adapter (for types Bosch- and Milwaukee battery)
- **Art.-no: 447491**
- Battery type Makita 18V / 4,0 Ah (no adapter needed)
can be ordered as accessory (art.nr: 447810)

