

ALPHA 630, Floor-mounted cabinet, Flat Pack, IP43, Protection class 1, H: 1900 mm, W: 550 mm, T: 210 mm, RAL 7035



| Versie                     |                |
|----------------------------|----------------|
| productmerksnaam           | ALPHA 630      |
| productbenaming            | staande kast   |
| uitvoering van het product | Flat Pack      |
| oppervlaktebehandeling     | poedergespoten |

  

| Beschermingsklasse                                  |      |
|---|------|
| beschermingsklasse IP                               | IP43 |
| geschiktheid voor samenwerking / bliksembeveiliging | Ja   |
| geschiktheid voor gebruik / voor gebruik buiten     | Geen |

  

| Verschijning                                      |          |
|---|----------|
| RAL-kleurnummer                                   | RAL 7035 |
| productbestanddeel                                |          |
| • kabelinvoer                                     | Ja       |
| • montageplaat                                    | Geen     |
| productuitbreiding / optioneel / aaneenschakeling | Ja       |

  

| Mechanical Design |          |
|-------------------|----------|
| hoogte            | 1 900 mm |
| breedte           | 550 mm   |

|                              |         |
|------------------------------|---------|
| diepte                       | 210 mm  |
| inbouwdiepte                 | 210 mm  |
| nettogewicht                 | 37,5 kg |
| materiaal / van de behuizing | staal   |

## Certificaten

### referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

## other

[Miscellaneous](#)

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=8GK1302-8KK22>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/8GK1302-8KK22>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8GK1302-8KK22](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8GK1302-8KK22)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



