

EMC cabinet IP40 HxWxD=2000x 800x 800



Figure similar

| Wersja | |
|--|-----------|
| Nazwa markowa produktu | SIVACON |
| oznaczenie produktu | Szafa-EMV |
| wykonanie produktu / kompatybilny elektromagnetycznie | Tak |
| wykonanie szafy sterowniczej / wykonanie PC | Nigdy |
| wykonanie szafy sterowniczej / wykonanie pulpitu | Nigdy |
| Klasa ochrony | |
| Stopień ochrony IP | IP40 |
| możliwość zamontowania | |
| <ul style="list-style-type: none"> dla pomiarów w systemie metrycznym | M8 |
| możliwość zastosowania / do użytku zewnętrznego | Nigdy |
| Wygląd | |
| kod barwy RAL | RAL 7032 |
| element składowy produktu | |
| <ul style="list-style-type: none"> zdejmowana ramka | Nigdy |
| <ul style="list-style-type: none"> drzwi wentylacyjne | Nigdy |

| | |
|--|-------|
| • płyta montażowa | Nigdy |
| • tylne drzwi | Nigdy |
| • dach z przetłoczeniami wentylacyjnymi | Nigdy |
| • drzwi przezroczyste | Nigdy |
| • płyta montażowa z regulacją głębokości | Nigdy |
| liczba zamknięć | 1 |
| liczba drzwi | 1 |

Konstrukcja mechaniczna

| | |
|--|----------|
| wysokość | 2 000 mm |
| szerokość | 800 mm |
| głębokość | 800 mm |
| liczba jednostek podziału wysokości / dla wysokości montażowej | 38 |
| rodzaj montażu / 19-calowe osadzenie | Tak |
| masa netto | 175 kg |
| materiał | Stal |

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2

U

| General Product Approval | Declaration of Conformity | other |
|--------------------------|---------------------------|-------|
|--------------------------|---------------------------|-------|

[Miscellaneous](#)



Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF5088-4ES>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/8MF5088-4ES>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF5088-4ES

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>