

auxiliary current switch, 2 NC for miniature circuit breaker 5SL, 5SY, 5SP Incorporated switch 5TL1, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



| Versiyon   |                       |
|--|-----------------------|
| ürün marka adı   | SETRON                |
| ürün tanımı  | Yardımcı akım şalteri |
| ürün modeli  | takılabilir           |
| elektrikli işletim süresi (işletim çevrimleri) / tipik | 20 000                |
| IP koruma türü   | IP20                  |

| Ürün Detayı        |                 |
|--------------------|-----------------|
| ürün bileşeni      |                 |
| • yardımcı anahtar | Evet            |
| ürün ilavesi       | Yardımcı şalter |

| Numara                       |   |
|------------------------------|---|
| hata sinyali anahtarı sayısı | 0 |
| açıcı sayısı                 | 2 |
| kapayıcı sayısı              | 0 |
| değiştirici sayısı           | 0 |






| Bağlantılar                      |                             |
|----------------------------------|-----------------------------|
| bağlanabilir kablo kesiti        | 0,5 ... 2,5 mm <sup>2</sup> |
| sıkma torku / vida bağlantısında | 0,5 N·m                     |

bağlanabilir iletken kesit türü / AWG hatlarında 24 ... 12

## Mekanik Tasarım

|                      |                |
|----------------------|----------------|
| yükseklik            | 90 mm          |
| genişlik             | 9 mm           |
| derinlik             | 70 mm          |
| net ağırlık          | 67 g           |
| • işletim sırasında  | -25 ... +55 °C |
| • depolama sırasında | -40 ... +75 °C |

## Sertifikalar

| General Product Approval   | Declaration of Conformity   | Test Certificates  | Shipping Approval   |
|--|---|--|---|
| <br>CCC | <br>UR | <br>VDE | <br>EG-Konf. |
|  |   | <a href="#">Miscellaneous</a>  | <br>LRS    |

| other                         | Railway                             |
|-------------------------------|-------------------------------------|
| <a href="#">Miscellaneous</a> | <a href="#">Vibration and Shock</a> |

## Diğer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5ST3012>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/5ST3012>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5ST3012](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3012)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

