

MINIZED, Switch disconnecter with Fuse, D02, 3P+N, In: 63 A, Un  
AC: 400 V



### Versiyon

ürün marka adı MINIZED

### Genel teknik veriler

kutup sayısı 4  
kutup sayısı / not 3P+N  
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca D02  
aşırı gerilim kategorisi 4

### Gerilim

şok gerilim mukavemeti / anma değeri 6 kV

### Besleme gerilimi

akım / AC'de / anma değeri 63 A  
işletim gerilimi / AC'de / anma değeri 400 V

### Koruma sınıfı

IP koruma türü IP20, bağlı iletkenlerle birlikte

### Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak  
işletim durumunda / kutup başına 9 W

## Ürün Detayı

ürün özelliği / mühürlenebilir Evet

## Bağlantılar

sıkma torku / vida bağlantısında 2,5 ... 3 N·m

## Mekanik Tasarım

yükseklik	70 mm
genişlik	108 mm
derinlik	90 mm
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	524 g

## Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval	other
--------------------------	---------------------------	-------------------	-------------------	-------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)



GL

[Miscellaneous](#)

## Diğer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG7163>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG7163>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG7163](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG7163)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



