

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 300 mm, T: 250 mm, RAL 7035



| версия  |                            |
|---|----------------------------|
| Фирменное название продукта                                       | ALPHA 630                  |
| Наименование продукта   | Напольный шкаф             |
| Исполнение продукта   | С открытой боковой стенкой |
| Обработка поверхности   | порошковая окраска         |
| класс защиты  |                            |
| Степень защиты IP   | IP55                       |
| Пригодность к взаимодействию / молниезащита                       | да                         |
| Пригодность к использованию / для внешнего использования          | нет                        |
| появление   |                            |
| Номер цвета RAL   | RAL 7035                   |
| Компонент продукта  |                            |
| • Кабельный ввод  | да                         |
| • монтажная плита   | нет                        |
| Расширение продукта / дополнительно / последовательное соединение | да                         |
| Механическая конструкция  |                            |

|                    |          |
|--------------------|----------|
| Высота             | 1 950 mm |
| Ширина             | 300 mm   |
| Глубина            | 250 mm   |
| Монтажная глубина  | 250 mm   |
| вес-нетто          | 26,5 kg  |
| Материал / корпуса | сталь    |

## Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

### other

[Miscellaneous](#)

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1323-8KP13>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1323-8KP13>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KP13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP13)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



