

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** V-TAC

**Supplier's address:** V-TAC Europe, bul. Rozhen 41, Sofia, BG

**Model identifier:** 2125966

## Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	+ve and -ve (because strips are DC voltage and have black and red wires)		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

## Product parameters

Parameter	Value	Parameter	Value
<b>General product parameters:</b>			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	12	Energy efficiency class	F
Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	1 380 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power ( $P_{on}$ ), expressed in W	12,0	Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal	0,00
Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90
Outer dimensions without	Height	Spectral power distribution in the	See image in last page
	Width		
			8

separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)	Depth	1 000	range 250 nm to 800 nm, at full-load	
Claim of equivalent power <sup>(a)</sup>		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,431 0,396
<b>Parameters for LED and OLED light sources:</b>				
R9 colour rendering index value		62	Survival factor	1,00
the lumen maintenance factor		0,96		

(a) '-': not applicable;

(b) '-': not applicable;



Model placed on the Union market from 05/07/2025.



**EPREL registration number:** 2407754

<https://eprel.ec.europa.eu/qr/2407754>

**Supplier:** V-TAC Europe Ltd (Manufacturer)

**Website:** [www.v-tac.eu](http://www.v-tac.eu)

**Customer care service:**

**Name:** V-TAC Europe

**Website:** [www.v-tac.eu](http://www.v-tac.eu)

**Email:** [office@v-tac.eu](mailto:office@v-tac.eu)

**Phone:** +359290566

**Address:**

bul. Rozhen 41

Sofia

Bulgaria