









Niete

| DIN | Maße                                                                              | 2          | 2,5  | 3    | 4    | 5    | 6    | 7    | 8    | 10 * |
|-----|-----------------------------------------------------------------------------------|------------|------|------|------|------|------|------|------|------|
| 660 |  | 3,5        | 4,4  | 5,2  | 7    | 8,8  | 10,5 | 12,2 | 14   | 16   |
|     | $d_{3\min}$                                                                       | 1,87       | 2,37 | 2,87 | 3,87 | 4,82 | 5,82 | 6,82 | 7,76 | 9,4  |
| 661 |  | $e_{\max}$ | 1    | 1,25 | 1,5  | 2    | 2,5  | 3    | 3,5  | 4    |
|     | $k_{660}$                                                                         | 1,2        | 1,5  | 1,8  | 2,4  | 3    | 3,6  | 4,2  | 4,8  | 6,5  |
|     | $K_{661}$                                                                         | 1          | 1,2  | 1,4  | 2    | 2,5  | 3    | 3,5  | 4    | -    |

\* Maßangaben entsprechen DIN 124

| DIN | Maße                                                                              | 2    | 2,5  | 3    | 3,5  | 4    | 5    | 6    |
|-----|-----------------------------------------------------------------------------------|------|------|------|------|------|------|------|
| 662 |  | 4    | 5    | 6    | 7    | 8    | 10   | 12   |
|     | $d_{3\min}$                                                                       | 1,87 | 2,37 | 2,87 | 3,37 | 3,87 | 4,82 | 5,82 |
|     | $e_{\max}$                                                                        | 1    | 1,25 | 1,5  | 1,75 | 2    | 2,5  | 3    |
|     | k                                                                                 | 1    | 1,2  | 1,5  | 1,8  | 2,1  | 2,5  | 3    |
|     | w                                                                                 | 0,7  | 0,8  | 1    | 1,2  | 1,4  | 1,7  | 2    |

| DIN | Maße                                                                              | 3    | 4    | 5    | 6    |
|-----|-----------------------------------------------------------------------------------|------|------|------|------|
| 674 |  | 6,8  | 9    | 11,2 | 13,5 |
|     | $d_{3\min}$                                                                       | 2,87 | 3,87 | 4,82 | 5,82 |
|     | $e_{\max}$                                                                        | 1,5  | 2    | 2,5  | 3    |
|     | k                                                                                 | 1,5  | 2    | 2,5  | 3    |

| DIN    | Maße                                                                                | 3    | 4   | 5   | 6    | 8    |
|--------|-------------------------------------------------------------------------------------|------|-----|-----|------|------|
| 7338 B |  | 5,5  | 7,5 | 9,5 | 11,5 | 15,5 |
|        | $d_{3\min}$                                                                         | 2,85 | 3,8 | 4,8 | 5,8  | 7,75 |
|        | $d_4$                                                                               | 1,7  | 2,7 | 3,5 | 4,2  | 6    |
|        | $e_{\max}$                                                                          | 1,5  | 2   | 2,5 | 3    | 4    |
| 7338 C |  | k    | 0,8 | 1   | 1,2  | 1,2  |
|        | $r_{\max}$                                                                          | 0,2  | 0,3 | 0,3 | 0,4  | 0,4  |
|        | s                                                                                   | 0,5  | 0,5 | 0,6 | 0,75 | 1,2  |