










Kühlkörper für DIL-IC und PLCC

Kühlkörper für DIL-IC






– andere Längen auf Anfrage

							
Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]	Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]
ICK 6 8 L	6/8 polig	8,5	83	ICK 20 L	20 polig	25,0	34
ICK 14 16 L	14/16 polig	19,0	46				
							
Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]	Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]
ICK 14 16 B	14/16 polig	6,3	54,0	ICK 36 B	36 polig	47,0	16,5
ICK 24 B	24 polig	33,0	19,4	ICK 40 B	40 polig	51,0	15,8
ICK 28 B	28 polig	37,0	18,5	ICK 1000 B	—	1000,0	—
Oberfläche:		schwarz eloxiert					

– mit Klemmbügel
– andere Längen auf Anfrage

							
Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]	Art. Nr.	für Gehäuse	↔ [mm]	R_{th} [K/W]
ICK 14 H	14 polig	18,0	20	ICK 18 H	18 polig	23,0	16
ICK 16 H	16 polig	20,5	18	ICK 1000 H	—	1000,0	—
Oberfläche:		schwarz eloxiert					

Kühlkörper für PLCC

						
Art. Nr.	R_{th} [K/W]					
ICK R	19					
						
Art. Nr.	↔ [mm]	R_{th} [K/W]				
ICK PLCC 28	11,8	25				
Oberfläche:		schwarz eloxiert				